

Cable reel - SAC-3P-100,0-534/0,75 - 1457432

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable ring, PVC black, 3-pos., conductor colors: black 1-2/green-yellow, cable length: 100 m

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 617567
GTIN	4046356617567

Technical data

Dimensions

Length of cable	100 m
-----------------	-------

General

Number of positions	3
---------------------	---

Cable

Cable type	PVC, 0.75 mm ² , black
Cable type (abbreviation)	534
Conductor cross section	3x 0.75 mm ² (Signal line)
AWG signal line	18
Conductor structure signal line	24x 0.20 mm
Core diameter including insulation	1.7 mm ±0.1 mm
Wire colors	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
External sheath, color	black
External cable diameter D	5.3 mm ±0.2 mm
Minimum bending radius, fixed installation	5 x D
Outer sheath, material	PVC
Material conductor insulation	PVC

Cable reel - SAC-3P-100,0-534/0,75 - 1457432


Technical data

Cable

Conductor material	Bare Cu litz wires
Insulation resistance	min. 20 MΩ*km (at 20 °C)
Conductor resistance	26 Ω/km (at 20 °C)
Nominal voltage, cable	300 V
Test voltage, cable	1200 V
Flame resistance	DIN VDE 0482
	DIN EN 50265-2-1
	in acc. to UL VW1
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (cable, flexible installation)

Drawings

Cable cross section



PVC [534]

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	--	---------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>