


Cable Assemblies



Stress-Relieved/Weatherproof Cable Assemblies		
RG58C/U — 50 Ohm, BNC male each end.		
885-0500, 2249-C-12, 12"	EACH	11.75
885-0501, 2249-C-24, 24"	EACH	11.75
885-0502, 2249-C-36, 36"	EACH	11.75
885-2252, 2249-C-48, 48"	EACH	14.65
885-2253, 2249-C-60, 60"	EACH	14.65
885-0503, 2249-C-72, 72"	EACH	14.65
885-0504, 2249-C-120, 120"	EACH	17.60
885-0505, 2249-C-180, 180"	EACH	21.25
885-2261, 2249-C-240, 240"	EACH	24.95
RG59B/U-75 Ohm, BNC male each end.		
885-2256, 2249-E-12, 12"	EACH	12.50
885-2254, 2249-E-36, 36"	EACH	12.50
885-2257, 2249-E-48, 48"	EACH	14.70
885-2255, 2249-E-60, 60"	EACH	14.70
885-2260, 2249-E-72, 72"	EACH	14.70
885-2262, 2249-E-120, 120"	EACH	17.65
885-2263, 2249-E-180, 180"	EACH	21.30


Low Noise BNC Male Each End with Boot		
Frequency Range: DC to 10 kHz		
885-4964, 4964-SS-24, 24"	EACH	15.75
885-4965, 4964-SS-36, 36"	EACH	15.75
885-4966, 4964-SS-48, 48"	EACH	19.00
885-4967, 4964-SS-60, 60"	EACH	19.00
885-4968, 4964-SS-72, 72"	EACH	19.55

BNC Male 50 Ohm Cable




885-6010, 5697-12, 12"	EACH	6.30
885-6012, 5697-24, 24"	EACH	6.30
885-7004, 5697-36, 36"	EACH	6.30
885-7005, 5697-48, 48"	EACH	9.15
885-7006, 5697-60, 60"	EACH	9.15
885-7007, 5697-72, 72"	EACH	9.15
885-6011, 5697-120, 120"	EACH	11.05

BNC Male Each End/RG58C/U — 50 Ohms



885-0035, BNC-C-18, 18"	EACH	13.58
885-0036, BNC-C-24, 24"	EACH	13.45
885-0008, BNC-C-36, 36"	EACH	13.45
885-0037, BNC-C-48, 48"	EACH	15.25
885-0009, BNC-C-60, 60"	EACH	15.25

BNC Male to SMA Male



885-4015, 4935-BB-24, 24"	EACH	34.95
885-4935, 4935-BB-48, 48"	EACH	34.95
885-4936, 4935-BB-60, 60"	EACH	34.95

SMA Male Each End, 50 Ohm Cable




RG174/U, Rating: +85°C max. 0.100" O.D.		
885-4840, 4846-K-24, 24"	EACH	34.35
885-4841, 4846-K-48, 48"	EACH	34.35
885-4842, 4846-K-60, 60"	EACH	34.35

RG316/U, Rating: +200°C max. 0.098" O.D.		
885-4843, 4846-BB-24, 24"	EACH	38.45
885-4846, 4846-BB-48, 48"	EACH	38.45
885-4844, 4846-BB-60, 60"	EACH	38.45


RG142B/U, Rating: +200°C max. 0.100" O.D.		
885-4845, 4846-X-24, 24"	EACH	51.00
885-4847, 4846-X-48, 48"	EACH	51.00
885-4848, 4846-X-60, 60"	EACH	51.00

Double Banana Plug, Each End




885-6190, 2BA-18, Two Cond. Twisted Pr. 18"	EACH	13.75
885-6191, 2BA-24, Two Cond. Twisted Pr. 24"	EACH	13.75
885-6017, 2BA-36, Two Cond. Twisted Pr. 36"	EACH	13.75
885-6038, 2BA-48, Two Cond. Twisted Pr. 48"	EACH	15.25
885-6192, 2BA-60, Two Cond. Twisted Pr. 60"	EACH	15.25
885-6216, 2BC-18, RG58C/U, 18"	EACH	12.90
885-0205, 2BC-24, RG58C/U, 24"	EACH	12.90
885-6029, 2BC-36, RG58C/U, 36"	EACH	12.90
885-6217, 2BC-48, RG58C/U, 48"	EACH	13.95
885-6218, 2BC-60, RG58C/U, 60"	EACH	13.95

Double Banana Plug, One End Only




885-6003, 1326-A-60, Two Cond. Twisted Pr. 60"	EACH	11.62
885-1326, 1326-C-60, RG58C/U, 60"	EACH	11.62

Type "N" Male, Each End




885-1650, 1658-T-18, RG214/U, 18"	EACH	40.00
885-1651, 1658-T-24, RG214/U, 24"	EACH	40.00
885-1652, 1658-T-36, RG214/U, 36"	EACH	40.00
885-1654, 1658-T-60, RG214/U, 60"	EACH	61.00

BNC Male to Double Banana Plug




885-4530, 4530-C-18, 18"	EACH	13.35
885-4531, 4530-C-24, 24"	EACH	13.35
885-4532, 4530-C-36, 36"	EACH	13.35
885-4533, 4530-C-48, 48"	EACH	14.80
885-4534, 4530-C-60, 60"	EACH	14.80

Banana Plugs to Double Banana Plug




885-1300, 1368-A-18, 18"	EACH	21.40
885-1301, 1368-A-24, 24"	EACH	21.40
885-1302, 1368-A-30, 30"	EACH	21.40
885-1303, 1368-A-36, 36"	EACH	21.40
885-4036, 1368-A-48, 48"	EACH	22.45
885-1304, 1368-A-60, 60"	EACH	22.45

Minigrabber® Test Clips to Double Banana Plug




1st End: Minigrabber®, Contact: Beryllium copper, gold plated. Insulation: Glass filled nylon. One black and one red. Cable: Shielded coax., RG58C/U, 4.95 mm (0.195) O.D. Y-Mold Insulation: PVC, black. 2nd End: Banana plug. Brass body, beryllium copper spring, nickel plated. Insulation: Polyethylene, black. Rating: 45 VAC; +50°C (+122°F) max.		
885-0936, 3786-C-18, Black/Red, 18"	EACH	13.65
885-0937, 3786-C-24, Black/Red, 24"	EACH	13.65
885-0960, 3786-C-36, Black/Red, 36"	EACH	13.65
885-0961, 3786-C-48, Black/Red, 48"	EACH	14.70
885-0962, 3786-C-60, Black/Red, 60"	EACH	14.70

BNC Male with Boot Patch Cords to Minigrabber® Test Clips



885-5180, 5187-C-24, 24", 58C	EACH	14.50
885-5181, 5187-K-24, 24", 174	EACH	20.15
885-5182, 5187-C-36, 36", 58C	EACH	14.50
885-5183, 5187-K-36, 36", 174	EACH	20.15
885-5184, 5187-C-48, 48", 58C	EACH	14.50
885-5185, 5187-K-48, 48", 174	EACH	20.15


BNC Breakouts



BNC Male to Test Clips — Fig. A	
885-0654, 2886, BNC Male to Minigrabber Clips	EACH 11.55
BNC Female to Test Clips — Fig. B	
885-2630, 2630, BNC Female to Alligator Clips	EACH 8.50
885-0625, 2631, BNC Female to Minigrabber Clips	EACH 8.50
BNC Female to Pin Tip Plugs — Fig. C	
885-3221, 3221	EACH 9.15
BNC Female to Stacking Banana Plugs — Fig. D	
885-3073, 3073	EACH 7.90
BNC Male to Stacking Banana Plugs — Fig. D	
885-6005, 3957	EACH 11.45
BNC Female to MINIGRABBER® Test Clips — Fig. E	
885-3788, 3788	EACH 8.20
BNC Male to MINIGRABBER® Test Clips — Fig. E	
885-3700, 3789	EACH 10.10
BNC Male to 20 AWG Leads — Fig. F	
885-4970, 4970	EACH 7.65
BNC Female to 20 AWG Leads — Fig. G	
885-4969, 4969	EACH 5.55

SMD Products

SMD GRABBER™, Each End




1st End: SMD GRABBER®, Contact: Selectively gold plated stainless steel. Insulation: Glass filled nylon. Wire: 22 AWG, 26 × 36 t.c., PVC insulated, 1.63 mm (0.064) O.D. 2nd End: Same as first end. Rating: 45 VAC; 0.5 amps; +102°C (+216°F) max.		
885-5230, 5301-12-0, Black, 12"	EACH	5.80
885-5235, 5301-12-2, Red, 12"	EACH	5.80
885-5240, 5301-24-0, Black, 24"	EACH	5.80
885-5245, 5301-24-2, Red, 24"	EACH	5.80
885-5250, 5301-36-0, Black, 36"	EACH	5.80
885-5255, 5301-36-2, Red, 36"	EACH	5.80

SMD GRABBER® Test Clip Patch Cord Kit


Kit contains 10 pieces of model 5301-24, one each of ten colors.	
885-6044, 5521	EACH 53.00

SMD GRABBER™ to Stacking Banana Plug




1st End: SMD GRABBER®, Contact: Selectively gold plated stainless steel. Insulation: Glass filled nylon. Wire: 22 AWG, 26 × 36 t.c., PVC insulated, 1.63 mm (0.064) O.D. 2nd End: Stacking Banana Plug. Brass body, beryllium copper spring, nickel plated. Polypropylene insulation. Rating: 45 VAC; 0.5 amps; +55°C (+131°F) max.		
885-5260, 5302-12-0, Black, 12"	EACH	5.45
885-5265, 5302-12-2, Red, 12"	EACH	5.45
885-5270, 5302-24-0, Black, 24"	EACH	5.45
885-5275, 5302-24-2, Red, 24"	EACH	5.45
885-5280, 5302-36-0, Black, 36"	EACH	5.45
885-5285, 5302-36-2, Red, 36"	EACH	5.45

SMD Test Tweezer™ to BNC Male



1st End: SMD Test Tweezer®, Tips: Beryllium copper, gold plated. Insulation: Glass filled nylon, black and red. Cable: Shielded coaxial, RG174/U, 2.54 mm (0.100) O.D. 2nd End: BNC Male. Brass body, tarnish resistant plated. Center Contact: Brass, gold plated. Boot: PVC, black. Rating: 45 VAC; 3 amps; +50°C (+122°F) max.		
885-5315, 5142-K-48	EACH	20.65

SMD Test Tweezer™ Leads to Multi-Stacking Banana Plugs



885-6271, 5143-K-48	EACH	20.65
---------------------	------	-------