



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	A $\pm .030$ $\pm (.762)$	B	C	WEIGHT lbs. / 100 (g) / pcs.
MP150	1.50 (38.1)	1.03 (26.2)	1.69 (42.9)	0.07 (30)
MP175	1.75 (44.4)	1.28 (32.5)	1.94 (49.3)	0.08 (36)
MP200	2.00 (50.8)	1.53 (38.9)	2.19 (55.6)	0.09 (30)
MP250	2.50 (63.5)	2.03 (51.6)	2.69 (68.3)	0.12 (55)
MP350	3.50 (88.9)	3.03 (77.7)	—	0.16 (75)



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- USE WITH ANY OF THESE TIES:
M=MINIATURE
I=INTERMEDIATE
S=STANDARD
- PART NO. & WEIGHT SHOWN SPECIFIES INDIVIDUAL PIECES, ADD SUFFIX "-R" TO PART NO. TO SPECIFY CONTINUOUS ROLLS OF 1000 PIECES. PART NO. MP350 IS NOT AVAILABLE IN ROLLS.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYER G00239GM_PB_MRKRLPLTE_01

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

**IDENTIFICATION
MARKER PLATE**

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

WHITE
NYLON

SCALE NONE

DATE 1/10/2000

CHK'D

DRAWING NO.

G00239GM

DWG

A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	10-22-01	LGG		TOOK OF +/- REF FROM 'B' & 'C' DUE TO ADDED 'REF' ON REV 2	G00239GM	2		
1	8/14/01	LGG		ADDED REF & UPDATED	G00239GM	1		
R	1-10-00	JAD		INITIAL RELEASE, REPLACES SS-4551 REV 5	G00239GM	R		