



Contact Configuration		
# of Contacts		6
Wire Color	1	Brown
	2	White
	3	Black
	4	Green
	5	Yellow
	6	Red
	7	--
	8	--

## Materials and Finish

Shell: steel, tin plated

Contacts: phosphor bronze, tin plated

Insulator: PBT, black  
UL94V-0 rated

Wire: 100mm, stripped ends, 26 AWG

Other wire lengths and termination options available, including customer specified headers. Contact Kycon for details.

## Specifications

Rating: 12V DC 2amp max.

Insulation Resistance: 50 Megohm min. at 250V DC

Dielectric Strength: 250v AC for 1 minute

Contact Resistance: 30 milliohm max.

Operating Temperature: -25°C to +80°C

Durability Rating: 5000 mating cycles min.

Housing Contact Retention: 3.0 lbs. min.

Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise

CSA NRTL/C Certified File No. LR78160

REVISION	DATE	DESCRIPTION	DRAWN BY	REV CHECK BY	UNITS	KMDPL-6S-400	Panel Mount Female Mini-DIN	KYCON
A2	1/30/02	ECO 01-146	K. Wallace	T. Gokcek	mm			
B1	5/16/02	ECO 02-040	REVISED BY	REV CHECK DATE	DATE			
B2	7/2/03	ECO 03-029	C. Leiva	7/2/03	4/6/99			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KMDPL-6S-400](#)