

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301040025](#)
Status: **Active**
Overview: Specialty Lighting
Description: Haztex Hazardous Location 26W with 12V Fluorescent Hand Lamp with In-line Transformer 16/3 SOOW Cord Type, Cord Length 7.62m (25.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR39801
 UL E30252

General

Product Family Portable Lighting
 Series [130104](#)
 Comments Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
 NEMA Configuration NEMA 5-15
 Outlet None
 Overview [Specialty Lighting](#)
 Product Name Haztex
 Type Hand Lamps, Specialty Light
 UPC 78678805476

Physical

Cord Length - Primary 7.62m (25.0')
 Cord Length - Secondary N/A
 Depth 100.08mm (3.940")
 Duty Hazardous
 Guard Included Yes
 Guard Type Cast Aluminum
 Height 482.60mm (19.000")
 Length N/A
 Material - Globe Tempered Soda-Lime Glass
 Material - Guard Cast Aluminum
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Fluorescent
 Cord Type - Primary 16/3 SOOW
 Lamp Type PL-C 26/41/4P
 Lamp Wattage - Maximum 26W
 Lumens 1800
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ
 Voltage (Secondary) - Maximum 12V AC

Material Info

Engineering Number 1090-HZ12IA163



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130104 Series](#)