

LOC		DIST		REVISIONS						
AA	27	P	F	ZONE	LTR	DESCRIPTION			DATE	APPD
					M	REV; EC 0210-0840-94			3-2-95	LM NJ


- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: POLYESTER FILM 0.025 [0.010] THICK.
2 LAYERS EACH SIDE.
COPPER WIRE- 0.23 [0.009] THICK × 15.24 [0.600] WIDE.
SHIELD- PVC, 0.025 [0.010] THICK.
- 3

CABLE MARKED WITH "AMP INC PN 553239
TYPE FCC UL CSA 12 AWG, CU 300V, 20 AMP 60°C"
IN COLOR SPECIFIED FOR CONTINUOUS LENGTH OF ROLL AS SHOWN.
- 4

CAUTION: THE UNDERCARPET CABLE MAY NOT BE USED OUTDOORS OR IN WET LOCATIONS; WHERE THE CABLE WOULD BE SUBJECT TO CORROSIVE VAPORS; IN ANY HAZARDOUS (CLASSIFIED) LOCATION; OR IN RESIDENTIAL, SCHOOL, AND HOSPITAL BUILDINGS.



30.7	[101]	3-553239-4
15.5	[51]	3-553239-3
76.5	[251]	3-553239-1
LENGTH PER ROLL - M (FEET)		PART NO

		LENGTH PER ROLL - M [FEET]		PART NO			
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± - MATERIAL 1		DR 2-18-94 B. SIMPSON		AMP AMP Incorporated Harrisburg, PA 17105-3608			
		CHK - C. WHITT					
		APPD - B. MCNEIL					
		APPD - D. MARGO					
2		PRODUCT SPEC 108-6038		NAME CABLE, FLAT, 5 CONDUCTOR, 12 AWG, POWER, UNDERCARPET			
FINISH -		APPLICATION SPEC 114-6008				SIZE D	
		WEIGHT -				CAGE CODE 00779	
				DRAWING NO C-553239			
				SCALE -			
				SHEET 1 OF 1			

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-553239-1](#)