


NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION:
INSULATOR: P.V.C. AVAILABLE IN BLACK OR RED.
CONTACT: ANACONDA 7021 OR BOILCAT C97.
GOLD PLATED.
SOCKET: BRASS. TIN PLATED.

2. PERFORMANCE:
MAXIMUM CURRENT: 13 AMPS
MAXIMUM VOLTAGE: 300 V
MAXIMUM TEMPERATURE: 122°F



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±	CONTRACT NO.		DESCRIPTION E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.
			APPROVALS	DATE	
			DRAWN R.L.	3/09	
			APPROVED BY		
		MATERIAL SEE NOTE.			E-Z-FLEX BAN SKT TO 0.062 [1.57] SKT ADAPTER (16AWG)
		FINISH SEE NOTE.			
NEXT ASSY	USED ON				
APPLICATION		DO NOT SCALE DRAWING			SCALE 2:1 SHEET 1 OF 1
					SIZE CODE IDENT NO. DRAWING NO. REV.
					A 08505 9336