


**Part Number: 87204-6368**

D-Subminiature Shielded I/O PCB Female Receptacle, Right Angle, Through Hole, 25 Circuits, M3 Inner Thread Screws Included, Gold (Au) Flash



Series image - Reference only

Status: **OBSOLETE**
Replacement: [482016368](#)
Series: [87204](#)
Category: I/O Connectors

Mates With Part(s):

[87203](#)

Product Environmental Compliance

[EU RoHS:](#) Compliance Status Not Reviewed

[China RoHS:](#)

[REACH SVHC:](#)

[Low-Halogen Status:](#) Not Reviewed

Part Detail**General**

Status	Obsolete
Category	I/O Connectors
Series	87204
Application	Wire-to-Board
Comments	Shell: Steel
Component Type	Receptacle
Product Name	D-Sub
Type	N/A

Physical

Circuits (Loaded)	25
Circuits (maximum)	25
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Orientation	Right Angle
PC Tail Length	3.18mm
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	2.77mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	300V

Material Info

UPC	800753750067
-----	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application

Tooling

[Check our list of old tooling that used to be available for this part](#)