

CATALOG LISTING
624HE5-RB
PAGE 1 OF 1

ISSUE
1

DDM/CAD
DRAWN

DCS
25 FEB 99

CHECK
JAF

25 FEB 99

CHECK

REVISIONS





CHECK


25 FEB 99

CHECK

RELEASE NO. PR-23756

REPLACES



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH				THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA			SCALE FULL
OPERATING FORCE — — — — 10 LB MAX		CONTACT ARRANGEMENT 4X SPDT			DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE --- 30 LB MAX					
RELEASE FORCE — — — — — 1 LB MIN		LOAD	28 VDC		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
PRETRAVEL — — — — — .020 — .030			SEA LEVEL	70,000 FT	
DIFFERENTIAL TRAVEL — — — .020 MAX			RES	7	
OVERTRAVEL — — — — — .200 MIN			IND	1	
			LAMP	2	
					WEIGHT 5.1 OZ MAX

- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 5
 - 3 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - 4 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - 5 - OPERATION IN TEMPERATURE RANGE OF -65°F (-55°C) TO +257°F (+125°C)
 - 6 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[624HE5-RB](#)