

## Wiha Insulated 1/2" Sockets & Sets



Inch - 6 &amp; 12 Point

SHOP

1000Volt

### 317 Insulated 1/2" Drive Sockets - 6 & 12 Point, Insulation

According to ASTM F-1505-01, DIN 7448 specification, up to 1000 Volt. Individually Tested. Chrome-vanadium steel, forged, oil-hardened.

| Item No. | Inch  | lbs. | pkg. |          |
|----------|-------|------|------|----------|
| 317 03   | 5/16  | .16  | 1    | 6 point  |
| 317 04   | 11/32 | .16  | 1    | 12 point |
| 317 05   | 3/8   | .16  | 1    | 12 point |
| 317 07   | 7/16  | .16  | 1    | 12 point |
| 317 08   | 1/2   | .16  | 1    | 12 point |
| 317 09   | 9/16  | .17  | 1    | 12 point |
| 317 10   | 5/8   | .19  | 1    | 12 point |
| 317 12   | 11/16 | .19  | 1    | 12 point |
| 317 13   | 3/4   | .21  | 1    | 12 point |
| 317 14   | 13/16 | .23  | 1    | 12 point |
| 317 15   | 7/8   | .26  | 1    | 12 point |
| 317 16   | 15/16 | .30  | 1    | 12 point |
| 317 18   | 1     | .32  | 1    | 12 point |
| 317 20   | 1-1/8 | .44  | 1    | 12 point |
| 317 22   | 1-1/4 | .58  | 1    | 12 point |

\*Sockets must be used with insulated ratchets & extensions



Metric - 6 Point

SHOP

1000Volt

### 316 Insulated 1/2" Drive Sockets - 6 Point, Insulation According to VDE, DIN 7448 specification, up to 1000 Volt. Individually Tested.

| Item No. | mm | lbs. | pkg. |  |
|----------|----|------|------|--|
| 316 08   | 8  | .15  | 1    |  |
| 316 09   | 9  | .15  | 1    |  |
| 316 10   | 10 | .16  | 1    |  |
| 316 11   | 11 | .16  | 1    |  |
| 316 12   | 12 | .16  | 1    |  |
| 316 13   | 13 | .17  | 1    |  |
| 316 14   | 14 | .17  | 1    |  |
| 316 15   | 15 | .17  | 1    |  |
| 316 16   | 16 | .19  | 1    |  |
| 316 17   | 17 | .19  | 1    |  |
| 316 18   | 18 | .20  | 1    |  |
| 316 19   | 19 | .21  | 1    |  |
| 316 20   | 20 | .25  | 1    |  |
| 316 21   | 21 | .25  | 1    |  |
| 316 22   | 22 | .28  | 1    |  |
| 316 23   | 23 | .29  | 1    |  |
| 316 24   | 24 | .30  | 1    |  |
| 316 26   | 26 | .37  | 1    |  |
| 316 27   | 27 | .41  | 1    |  |
| 316 28   | 28 | .44  | 1    |  |
| 316 30   | 30 | .51  | 1    |  |
| 316 32   | 32 | .55  | 1    |  |

\*Sockets must be used with insulated ratchets & extensions

NEW  
From Wiha

1000Volt

SHOP

### 317 90 24 Pc. Insulated 1/2" Drive Socket Set - Inch

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

#### Item No. 317 90 Set includes the following:

|                                                                      |  |
|----------------------------------------------------------------------|--|
| 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1" Sockets |  |
| 12858 1/2" x 125mm Extension Bar                                     |  |
| 11.63 12859 1/2" x 250mm Extension Bar                               |  |
| 12853 1/2" Ratchet - 260mm                                           |  |
| 15000 Insulated Electrician's Knife - 50mm                           |  |
| Slotted: 3.5, 4.5, 6.5mm & Phillips: 1, 2, 3                         |  |
| 32806 6.3" Long Nose Pliers                                          |  |
| 32818 8.0" Combo Pliers                                              |  |
| 32832 6.3" Diagonal Cutters                                          |  |



Metric

1000Volt

SHOP

### 316 91 24 Pc. Insulated 1/2" Drive Socket Set - Metric

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

#### Item No. 316 91 Set includes the following:

|                                                    |  |
|----------------------------------------------------|--|
| 8, 9, 10, 12, 13, 14, 15, 17, 19, 22, 24mm Sockets |  |
| 12858 1/2" x 125mm Extension Bar                   |  |
| 11.39 12859 1/2" x 250mm Extension Bar             |  |
| 12853 1/2" Ratchet - 260mm                         |  |
| 15000 Insulated Electrician's Knife - 50mm         |  |
| Slotted: 3.5, 4.5, 6.5mm & Phillips: 1, 2, 3       |  |
| 32806 6.3" Long Nose Pliers                        |  |
| 32818 8.0" Combo Pliers                            |  |
| 32832 6.3" Diagonal Cutters                        |  |