

[About AUO](#)
[Citizenship](#)
[Product Applications](#)
[Product Introduction](#)
[TFT-LCD](#)
[LCD TV](#)
[PID](#)
[Monitor](#)
[Mobile PC](#)
[e-Reader](#)
[General Display](#)
[Mobile Device](#)
[DSC](#)
[Printer](#)
[Car Display](#)
[PND](#)
[E-Paper](#)
[Solar Business](#)
[Technology](#)
[Investor Relations](#)
[Career](#)
[Support](#)

G057QN01 V2



General Display

Model G057QN01 V2

Size 5.7"

Resolution (pixel) QVGA (320 x 240)

Active Area 115.2 x 86.4

Pixel Pitch (mm) 0.36

Mode TN

Number of Colors 262K

Color Saturation (%) 50

Viewing Angle (H/V) 160 / 140

Brightness (cd/m²) 800

Contrast Ratio 800 : 1

Response Time (ms) 25

Power Consumption (W) 3.37

Interface CMOS

Supply Voltage (V) 3.3

Light Source LED

Outline Dimension (mm) 144 x 104.6 x 12.3

Weight (g) 160

Production Now

Remark Reverse Scan Replaceable Lightbar Wide Temperature

Related Links

[Technology](#)
[Awards](#)

Reference

[Contact AUO](#)