


# COST-EFFECTIVE & DUAL WIPE SOCKETS

(2.00 mm) .0787" PITCH • TLE/CLT SERIES



## TLE

### Mates:

TMMH, TMM, MTMM,  
MMT, TW, LTMM, ZLTMM,  
TCMD, TSH

## CLT

### Mates:

TMM, TMMH, MTMM,  
MMT, TW, TSH

## SPECIFICATIONS

### TLE

#### Insulator Material:

Black Liquid Crystal Polymer

#### Contact Material:

Phosphor Bronze

#### Plating:

Au over 50  $\mu$ " (1.27  $\mu$ m) Ni

#### Current Rating (TLE/TMMH):

3.2 A per pin  
(2 pins powered)

#### Operating Temp Range:

-55 °C to +125 °C

#### Insertion Depth:

(2.08 mm) .082" to  
(4.37 mm) .172" with  
(0.38 mm) .015" wipe,  
pass-through, or  
(3.35 mm) .132" min  
for bottom entry

### CLT

Same as TLE except:

#### Plating:

Sn or Au over 50  $\mu$ " (1.27  $\mu$ m) Ni

#### Current Rating (TMMH/CLT):

4.1 A per pin  
(2 pins powered)

#### Insertion Depth:

Top Entry=  
(1.40 mm) .055" minimum  
Bottom Entry=  
(2.57 mm) .101" minimum  
(add board thickness for  
correct post OAL)

#### Max Cycles:

100 with 10  $\mu$ " (0.25  $\mu$ m) Au

## PROCESSING

### TLE

#### Lead-Free Solderable:

Yes

#### SMT Lead Coplanarity:

(0.10 mm) .004" max (02-25)  
(0.15 mm) .006" max (27-50)\*  
\*(.004" stencil solution  
may be available; contact  
ipg@samtec.com)

### CLT

Same as TLE except:

#### SMT Lead Coplanarity:

(0.10 mm) .004" max (02-25)  
(0.15 mm) .006" max (26-34)\*  
(0.20 mm) .008" max (35-50)\*  
\*(.004" stencil solution  
may be available; contact  
ipg@samtec.com)

#### Note:

Some lengths, styles and  
options are non-standard,  
non-returnable.

| TLE | - 1 | NO. PINS PER ROW | - 01 | PLATING OPTION | - DV | OPTIONS |
|-----|-----|------------------|------|----------------|------|---------|
|-----|-----|------------------|------|----------------|------|---------|



02 thru 50

-G  
= 10  $\mu$ " (0.25  $\mu$ m)  
Gold



-A  
= Alignment Pin  
(3 positions minimum)

-K  
= (5.00 mm) .197" DIA  
Polyimide Film Pick & Place Pad  
(3 positions minimum)

-P  
= Metal Pick & Place Pad  
(4 positions minimum)

-TR  
= Tape & Reel Packaging  
(2-37 positions only)


-FR  
= Full Reel Tape & Reel  
(must order maximum  
quantity per reel; contact  
Samtec for quantity breaks)  
(2-37 positions only)



-P Option



-A Option



| CLT | - 1 | NO. PINS PER ROW | LEAD STYLE | PLATING OPTION | - D | OTHER OPTIONS |
|-----|-----|------------------|------------|----------------|-----|---------------|
|-----|-----|------------------|------------|----------------|-----|---------------|



02 thru 50

-01  
= Through-hole

-F  
= Gold flash  
on contact,  
Matte Tin on tail

All options require  
Style -02

-BE  
= Bottom Entry  
(Required for bottom  
entry applications)

-A  
= Alignment Pin  
(3 positions minimum)  
Metal or plastic at  
Samtec's discretion

-K  
= (5.00 mm) .197" DIA  
Polyimide Film  
Pick & Place Pad  
(04 thru 50 only)



-P  
= Pick & Place Pad  
(4 positions minimum)  
(Not always necessary  
for auto placement.)

-TR  
= Tape & Reel  
(36 positions max)

-FR  
= Full Reel Tape & Reel  
(must order maximum  
quantity per reel;  
contact Samtec for  
quantity breaks)  
(36 positions max)

ALSO AVAILABLE  
MOQ Required


Other Platings




-01 or -03



| LEAD STYLE | A           |
|------------|-------------|
| -01        | (2.16) .085 |
| -03        | (2.95) .116 |



-A Option



-P Option