

(1,27 mm) .050"

FTS SERIES

MICRO LOW PROFILE TERMINAL STRIPS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?FTS

HI-TEMP

Insulator Material:
Black Liquid Crystal Polymer

Terminal Material:
Phosphor Bronze

Operating Temp Range:
-55°C to +125°C

Plating:
Sn or Au over 50µ" (1,27 µm) Ni

RoHS Compliant:
Yes

Lead-Free Solderable:
Yes

SMT Lead Coplanarity:
.004" (0,10 mm) max


RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Mates with:
FFSD, CLP, FLE,
SFMC (LIF)

OPTIONS



Mates with
socket strips
or IDC cable

Surface
mount or
through-hole

Micro pitch
.050" x .050"
(1,27 mm x 1,27 mm)

Low profile
(1,27 mm) .050"

Shrouded and
alignment pin
options available

Impedance matched for
high speed applications

ALSO AVAILABLE (MOQ Required)

- Alignment pin
Contact Samtec.

FTS	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
02 thru 50 (except -S & -SA option = 05 thru 46)			-01 = .120" (3,05 mm) Post (Mates with FFSD) -02 = .075" (1,91 mm) Post (Mates with FLE) -03 = .065" (1,65 mm) Post (Mates with CLP)	-F = Gold flash on post, Matte Tin on tail -L = 10µ" (0,25 µm) Gold on post, Matte Tin on tail	-D = Double Through-hole -DV = Double Vertical SMT -S = Single Through-hole -SV = Single Vertical SMT	(-D & -DV only) -SA = End Shroud with Alignment Pin (05 thru 46 positions. Style -02 & -03 only) -S = End Shroud (05 thru 46 positions. Style -02 & -03 only) -P = Pick & Place Pad (05 positions minimum) -TR = Tape & Reel (-DV only) (Required callout for positions 2 thru 4)
No. of positions x .050 (1,27) + .325 (8,25) = -SA + .200 (5,08) = -S						

Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685