




2mm

LED CBI® Circuit Board Indicator (DIN 41494 Compatible), Bi-Level

Dialight

571-01xx



PART NO. WITHOUT PINS

COLOR*

571-0111
571-0112
571-0122
571-0132
571-0133

Red-Red
Red-Green
Green-Green
Yellow-Green
Yellow-Yellow

* Top-Bottom LED

PART NO. WITH PINS

COLOR*

571-0111-100
571-0112-100
571-0122-100
571-0132-100
571-0133-100


Red-Red
Red-Green
Green-Green
Yellow-Green
Yellow-Yellow

* Top-Bottom LED

Arrays available. See part number ordering code below.

Benefits

- DIN 41494 compatible
- Snaps into arrays
- Standard parts without pins also serve as end of row unit in arrays



-10x Suffix required only when ordering single units with pins or arrays



CLICK HERE

To Construct Custom Color Combinations of This Part



WITHOUT PINS
WITH PINS

Custom Combinations

- Contact factory for information on custom color combinations.

LED Data

- For absolute maximum ratings and other electrical/optical data, refer to LED data sheet.



Typical Operating Characteristics (TA=25°C)

Part Number	Color	Peak Wavelength nm	I _V * mcd	V _F ** Volts	Viewing Angle 2θ½	LED Data sheet	Page #
571-01xx	Red	635	12.6	2	38°	521-9630	3-13
	Green	565	8.7	2.1	38°	521-9632	3-13
	Yellow	585	12.6	2.1	38°	521-9631	3-13

* I_F = 10mA ** I_F = 20mA