


Model 2256 Patch Cord “N” (Male) Both Ends



Cable Types		
	RG 58C/U (Black)	RG 142B/U (Tinted Brown)
Model	2256-C-XX	2256-X-XX
Capacitance pf/ft.	30.8	29.0
Nominal Impedance	50	50
Temp	+80°C	+200°C

MATERIALS:

Conn: 1st end – Type “N” male, See table above.
 Finish: Body and Fitting, Tarnish resistant.
 Center contact-Gold plated per requirements of MIL-C-39012.
 Nominal Impedance: 50 Ohms.
 Cable: See table above. Marking: "POMONA 2256-X-XX".
 Conn: 2nd end – Same as first end.

RATINGS:

Operating Temperature: 2256-C-XX: +80°C (+176°F.) Max.
 2256-X-XX: +200°C (+440°F.) Max.
 Operating Voltage: 1000 VRMS Max.

ORDERING INFORMATION: Model 2256-X-XX

XX = Cable Lengths, Standard Length: 24" (610), 24" (610), 36" (914), 48" (1219) & 60" (1542).
 Additional lengths can be quoted upon request.
 Ordering Example: 2256-C-60 Indicates 60" in length

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[2256-X-48](#) [2256-C-60](#) [2256-C-48](#) [2256-C-24](#) [2256-X-36](#) [2256-X-24](#) [2256-X-60](#) [2256-C-36](#)