



Fixed Terminal Blocks

5.0mm Pitch




ELM Standard Profiles . . . Page 63
15A / 300V

5.0mm Pitch




ESLM Low-Profile, R/A . . . Page 65
13.5A / 300V

5.0mm Pitch



ESLT Multi-tier Pages 68-69
13.5A / 300V


5.0mm Pitch



ESMT Multi-tier Pages 70-71
17.5A / 300V


FIXED BLOCKS 5.0MM PITCH . . .

5.0mm Pitch



ESTT Multi-tier Pages 72-73
24A / 300V


5.0mm Pitch



SCM Spring-Clamp Page 81
20A / 300V


. . . FIXED BLOCKS 5.0MM PITCH

.200" Pitch



ELM Standard Profiles . . . Page 62
15A / 300V


.200" Pitch



ELMM Low-Profile, Angled. Page 64
15A / 300V


FIXED BLOCKS .200" PITCH . . .

.200" Pitch




ESLM Low-Profile, R/A . . . Page 65
13.5A / 300V

.200" Pitch




ESLT Multi-tier Pages 68-69
13.5A / 300V

.200" Pitch



ESMT Multi-tier Pages 70-71
17.5A / 300V


.200" Pitch



ESTT Multi-tier Pages 72-73
24A / 300V


. . . FIXED BLOCKS .200" PITCH . . .

.200" Pitch




ESTT 4-tier Page 67
24A / 300V

.200" Pitch




EL1M /2M /3M Page 66
20A / 300V

.200" Pitch



EL2M Right-Offset Page 67
20A / 300V

.200" Pitch





SCM Spring-Clamp Page 80
20A / 300V

. . . FIXED BLOCKS .200" PITCH



ESMT Multi-Tier Terminal Blocks Mid-Profile Modular Assembly

.200" (5.08mm)
5.0mm (.197")



1st / 2nd Tiers



3rd Tier Only



2nd Tier Only



	Pos	Catalog #	L		Pos	Catalog #	L		Pos	Catalog #	L
.200" Pitch				.200" Pitch				.200" Pitch			
Modules	4	ESMT04240	.400"	Modules	2	ESMT02230	.400"	Modules	2	ESMT02220	.400"
	6	ESMT06240	.600"		3	ESMT03230	.600"		3	ESMT03220	.600"
Assemblies	8	ESMT08240	.800"	Assemblies	4	ESMT04230	.800"	Assemblies	4	ESMT04220	.800"
	10	ESMT10240	1.000"		5	ESMT05230	1.000"		5	ESMT05220	1.000"
	12	ESMT12240	1.200"		6	ESMT06230	1.200"		6	ESMT06220	1.200"
	14	ESMT14240	1.400"		7	ESMT07230	1.400"		7	ESMT07220	1.400"
	16	ESMT16240	1.600"		8	ESMT08230	1.600"		8	ESMT08220	1.600"
	18	ESMT18240	1.800"		9	ESMT09230	1.800"		9	ESMT09220	1.800"
	20	ESMT20240	2.000"		10	ESMT10230	2.000"		10	ESMT10220	2.000"
	22	ESMT22240	2.200"		11	ESMT11230	2.200"		11	ESMT11220	2.200"
	24	ESMT24240	2.400"		12	ESMT12230	2.400"		12	ESMT12220	2.400"
5mm Pitch				5mm Pitch				5mm Pitch			
Modules	4	ESMT04140	10.2mm	Modules	2	ESMT02130	10.2mm	Modules	2	ESMT02120	10.2mm
	6	ESMT06140	15.2mm		3	ESMT03130	15.2mm		3	ESMT03120	15.2mm
Assemblies	8	ESMT08140	20.3mm	Assemblies	4	ESMT04130	20.3mm	Assemblies	4	ESMT04120	20.3mm
	10	ESMT10140	25.4mm		5	ESMT05130	25.4mm		5	ESMT05120	25.4mm
	12	ESMT12140	30.5mm		6	ESMT06130	30.5mm		6	ESMT06120	30.5mm
	14	ESMT14140	35.6mm		7	ESMT07130	35.6mm		7	ESMT07120	35.6mm
	16	ESMT16140	40.6mm		8	ESMT08130	40.6mm		8	ESMT08120	40.6mm
	18	ESMT18140	45.7mm		9	ESMT09130	45.7mm		9	ESMT09120	45.7mm
	20	ESMT20140	50.8mm		10	ESMT10130	50.8mm		10	ESMT10120	50.8mm
	22	ESMT22140	55.9mm		11	ESMT11130	55.9mm		11	ESMT11120	55.9mm
	24	ESMT24140	61.0mm		12	ESMT12130	61.0mm		12	ESMT12120	61.0mm

MATERIALS:

Housing: Polyamide 6/6, UL 94V-0, black

Contact: Copper alloy, tin-lead finish

Clamp Screw: Copper alloy, nickel finish

Wire clamp: Copper alloy, nickel finish

INSTALLATION:

Wire Range: 12-30 AWG

Wire Strip Length: .216-.256"

Recommended Tightening Torque: 4.4 lb-in. (0.5N-m)

Hole Diameter: .043 min.

Amphenol Pcd