

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74752-1701](#)
Status: **Active**
Overview: [SFP+ Passive Cable Assembly](#)
Description: SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 7.0m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E72548

General
Product Family Cable Assemblies
Series [74752](#)
Assembly Configuration Dual Ended Connectors
Comments Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector SFP Plus-to-SFP Plus
Overview [SFP+ Passive Cable Assembly](#)
Product Name SFP Plus
UPC 800756660899

Physical
Cable Length 7.0m
Circuits (Loaded) TWO DIFFERENTIAL PAIR
Gender Male-Male
Lock to Mating Part Yes
Material - Metal Beryllium Copper, Zinc Alloy
Net Weight 262.055/g
Packaging Type Bag
Single Ended No
Waterproof / Dustproof Yes
Wire Insulation Diameter N/A
Wire Size AWG 30
Wire/Cable Type Twin-ax

Electrical
Impedance 100#
Shield Type Full Shield
Shielded Yes
Voltage - Maximum 3.3V

Material Info

Reference - Drawing Numbers
Sales Drawing SD-74752-001



image - Reference only **Series**

EU RoHS
ELV and RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[74752Series](#)

Mates With
[74441](#) SFP Plus (SFP+) Host Connector