


# FUSE & FUSE HOLDERS

## FUSE HOLDERS

Fuse Block  
for 5.0 x 20mm Fuses



**Specifications:**  
**Electrical:** Rated for currents, up to 6.3A  
**Clip/terminals:** Nickel-plated tin-plated spring Brass ear type  
**Base:** Phenolic laminate or glass fiber  
**No. FH501**

Fuse Block  
for 5.0 x 20mm Fuses



**Specifications:**  
**Electrical:** Rated for currents, up to 6.3A  
**Clip/terminals:** Nickel-plated tin-plated spring Brass ear type  
**Base:** Phenolic laminate or glass fiber  
**No. FH503**

Fuse Block  
for 3AG Fuses



**Specifications:**  
**Electrical:** Rated for currents, up to 10A  
**Clip/terminals:** Nickel-plated tin-plated spring Brass ear type  
**Base:** Phenolic laminate or glass fiber  
**No. FH551**

Fuse Block  
for 3AG Fuses



**Specifications:**  
**Electrical:** Rated for currents, up to 10A  
**Clip/terminals:** Nickel-plated tin-plated spring Brass ear type  
**Base:** Phenolic laminate or glass fiber  
**No. FH554**

## Automotive Trailer Harnesses

These molded trailer harnesses are manufactured with a loop of 16AWG primary wire between the mating ends. We offer the most popular sizes for your custom installation needs.

**Specifications**  
**Connectors:** .156" Bullet plugs & sockets  
**Wire:** 16 AWG Automotive Primary wire  
**Body Material:** Molded Vinyl



**No. 65-1602**  
2 position flat, 12" loop  
(Brn, Red)



**No. 65-1603**  
3 position flat, 12" loop  
(Grn, Yel, Brn)




**No. 65-1604**  
4 position flat, 12" loop  
(Grn, Yel, Brn, Wht)



**No. 65-1624**  
4 position square, 12" loop  
(Grn, Brn, Yel, Wht)

## MAXI Fuses

These Buss™ fuses are suitable for use wherever Maxi Blade type fuses are specified. They are perfect for car stereo, Marine or General Automotive use. Made in U.S.A.



| Part Number | Amperage | Color  |
|-------------|----------|--------|
| MAX20A      | 20A      | Yellow |
| MAX30A      | 30A      | Green  |
| MAX40A      | 40A      | Orange |
| MAX50A      | 50A      | Red    |
| MAX60A      | 60A      | Blue   |
| MAX80A      | 80A      | Clear  |

Buss is a registered trademark of Cooper/Bussman Industries

## AGU Heavy Duty In-line Fuse Holder

Heavy Duty Spring loaded Fuse holder for AGU or AG Glass fuses. It has machine brass contacts in a bakelite housing with a 12" loop of 8 AWG wire.



**No. FH8600**

## ATC Style In-line Fuse Holder

This is a heavy duty fuse holder to be used with ATC, ATO, and ATG blade type fuses. The wire is 10 AWG automotive primary wire in a 12" loop.



**No. FH1040**

## Maxi Style In-line Fuse Holder

A heavy duty in-line fuse designed for the MAXI style fuses. It is constructed from 8 AWG automotive power cable, and has a screw hole for easy mounting. The fuse holder is rated for up to 80A.



**No. FHMAXI**

## FUSES




**Dimensions** - 1/4" x 1-1/4"  
**Voltage Rating** - 250V AC  
**Test Conditions** - Grade A U.L. Listed up to 7.0 amps.  
Display packaged of (5) pcs.

|              | Current (amps) |
|--------------|----------------|
| No. 3AG1/4   | 1/4            |
| No. 3AG1/2   | 1/2            |
| No. 3AG3/4   | 3/4            |
| No. 3AG1     | 1              |
| No. 3AG1-1/2 | 1-1/2          |
| No. 3AG2     | 2              |
| No. 3AG3     | 3              |
| No. 3AG4     | 4              |
| No. 3AG5     | 5              |
| No. 3AG7-1/2 | 7-1/2          |
| No. 3AG10    | 10             |
| No. 3AG15    | 15             |
| No. 3AG20    | 20             |
| No. 3AG25    | 25             |
| No. 3AG30    | 30             |

## EUROPEAN FUSES GMA TYPE


Dimensions - 5mm O.D. x 20mm length.  
Replacement fuse for foreign equipment.  
Display package of 5 pcs.  
Voltage Rating: 250V AC



| No.    | Current | No.    | Current |
|--------|---------|--------|---------|
| EF1005 | .5A     | EF1050 | 5.0A    |
| EF1010 | 1.0A    | EF1060 | 6.0A    |
| EF1015 | 1.5A    | EF1080 | 8.0A    |
| EF1020 | 2.0A    | EF1100 | 10.0A   |
| EF1025 | 2.5A    | EF1150 | 15.0A   |
| EF1030 | 3.0A    |        |         |
| EF1040 | 4.0A    |        |         |

## SFE SERIES AUTO FUSES

**Voltage Rating** - 32V  
Display package of (5) pcs.



| No.    | Current | Size           |
|--------|---------|----------------|
| SFE4A  | 4A      | 1/4" x 5/8"    |
| SFE6A  | 6A      | 1/4" x 3/4"    |
| SFE75A | 7-1/2A  | 1/4" x 7/8"    |
| SFE9A  | 9A      | 1/4" x 7/8"    |
| SFE14A | 14A     | 1/4" x 1-1/16" |
| SFE20A | 20A     | 1/4" x 1-1/4"  |
| SFE30A | 30A     | 1/4" x 1-7/16" |

## FUSE PULLER and INSERTION TOOL



### No. P100

Durable plastic tool for removal of all 5mm and 1/4" diameter glass fuses. 2nd end allows user to remove and insert blade type fuses.

## Gold AGU / 5 AG TYPE FUSES

For HI-FI, Auto high Current Fuses, Custom Installation.



13/32" D x 1-1/2" L.  
(32V) 15A, 20A, 25A, 30A, 35A, 40A, 50A & 60A.  
Display Package of 2 Pcs.

| No.  | Current | Voltages |
|------|---------|----------|
| 8615 | 15A     | 32V      |
| 8620 | 20A     | 32V      |
| 8625 | 25A     | 32V      |
| 8630 | 30A     | 32V      |
| 8635 | 35A     | 32V      |
| 8640 | 40A     | 32V      |
| 8650 | 50A     | 32V      |
| 8660 | 60A     | 32V      |

## BLADE TYPE TERMINAL FUSES

**Voltage Rating** - 32V

Suitable for American cars. Display package of (5) pcs.



| No.   | Current (amps) |
|-------|----------------|
| PAP3  | 3 Purple       |
| PAP5  | 5 Tan          |
| PAP75 | 7.5 Brown      |
| PAP10 | 10 Red         |
| PAP15 | 15 Blue        |
| PAP20 | 20 Yellow      |
| PAP25 | 25 Clear       |
| PAP30 | 30 Green       |

**EMERGENCY KIT**  
Contains 1 each of value fuse in display package.  
**No. PAP8**

## SLO-BLO



**Dimensions:**  
1/4" x 1-1/4"  
**Voltage Rating:**  
250V AC  
**Test Conditions:**  
Grade A U.L. Listed up to 7.0 amps.  
Display Package of (2) pcs.  

| No.     | Current |
|---------|---------|
| SB1     | 1A      |
| SB2     | 2A      |
| SB3     | 3A      |
| SB5     | 5A      |
| SB7-1/2 | 7-1/2A  |
| SB10    | 10A     |