







RECOMMENDED PC BOARD LAYOUT

- ▲ NYLON, UL 94V-0 RATED, RED.
- ▲ BRASS PER ASTM B36.
- ▲ 3.81µm [.000150] MIN TIN OVER 2.54µm [.000100] MIN COPPER.
- ▲ 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- ▲ .000150 MIN TIN OVER .000100 MIN CU, OR .000050 MIN NICKEL.

OBSOLETE	▲	YES	207121-8
	▲	NO	207121-4
	▲	YES	207121-3
	▲	NO	207121-2
	▲	YES	207121-1

CONTACT FINISH	MOUNTING TABS	PART NO
----------------	---------------	---------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE: 03/12/01	BY: [Signature]	APP: [Signature]	DATE: 3-17-02	NAME: [Signature]	DATE: 3-17-02	NAME: [Signature]
DIMENSIONS: INCHES		TOLERANCES UNLESS SPECIFIED:		STANDARD SPEC:		APPLICATION SPEC:		SIZE: 108-10033
MATERIAL: HOUSING: ▲		FINISH: CONTACT: SEE TABLE		REWORK: -		SIZE: A1		DATE CODE: 00779
CUSTOMER DRAWING		SCALE: 4:1		SHEET: 1 OF 1		REV: W		RESTRICTED TO: -