


ACHF CONNECTOR



1.2mm pitch/Disconnectable Crimp style connectors



This ACHF connector is compact and low profile type, height 1.43mm and width 4.95mm, 1.2mm pitch wire-to-board connector.

- High-strength
- Top entry but side feed type
- Connector for power supply (Power supply circuit: 2.5 A, Signal circuit: 1.0 A)

Specifications -

• Current rating: 2.5 A AC, DC (AWG #28)

(Signal circuit of 4 and 6 circuits is 1.0 A.)

					C	Current unit: A
Circuit No.	1	2	3	4	5	6
3	2.5	2.5	2.5			
4	2.5	1.0	1.0	2.5		
6	2.5	2.5	1.0	1.0	2.5	2.5

• Voltage rating: 50 VAC, DC

• Temperature range: -25°C to +85°C

(including temperature rise in applying

electrical current)

• Contact resistance: Initial value/ 10 m Ω max.

After environmental tests/ 20 m Ω max.

• Insulation resistance: 100 $\,\Omega$ min. • Withstanding voltage: 500 VAC/minute


 Applicable wire: Conductor size/ AWG #30 to #28 Insulation O.D./ 0.5 to 0.63 mm

- * Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.
- * Contact JST for details.
- * Compliant with RoHS.


Standards-

Recognized E60389

PC board layout and Assembly layout




Cir	Circuits	Dimensions (mm)			
	Circuits	Α	В		
	3	2.4	5.5		
	4	3.6	6.7		
	6	6.0	9.1		



Note: 1. The above figure is the figure viewed from the connector mounting side.

2. Tolerances are non-cumulative: ±0.05 mm for all centers. The dimensions above should serve as a guideline. Contact JST for details.

Contact



Model No.	Applicable wire		Insulation O.D. (mm)	O'ty/rool
Model No.	mm ²	AWG#	insulation O.D. (IIIII)	Q ty/leel
SACHF-003GAC-P0.2	0.05~0.08	30~28	0.5~0.63	40,000

Material and Finish


Copper alloy, nickel-undercoated, gold-plated

RoHS compliance

	2	Crimping	Applicator				
Contact		machine	Crimp applicator	Dies	Crimp applicator with dies		
	SACHF-003GAC-P0.2	VD KON	MKS-L-10-4	MK/SACHF-003-02	APLMK SACHF003-02		
SACHT-003GAC-P0.2	AF-NZIN	_	_	_			

ACHF CONNECTOR

Housing




0: :	Model No.	Dimensions (mm)		Q'ty/
Circuits		А	В	bag
3	ACHFR-03V-H	2.4	3.8	1,000
4	ACHFR-04V-H	3.6	5.0	1,000
6	ACHFR-06V-H	6.0	7.4	1,000

Material

PBT, UL94V-HB, gray

RoHS compliance

Shrouded header



Circuits	Model No.	Dimensions (mm)		Q'ty/
		Α	В	reel
3	BM03B-ACHFKS-GACN-ETF	2.4	6.1	6,000
4	BM04B-ACHFKS-GACN-ETF	3.6	7.3	6,000
6	BM06B-ACHFKS-GACN-ETF	6.0	9.7	6,000

Material and Finish

Contact: Copper alloy, nickel-undercoated, gold-plated (nickel-stripe)
Housing: Heat resisting resin, UL94V-0, black
Reinforcement: Copper alloy, copper-undercoated, tin-plated (reflow treatment)

RoHS compliance This product displays (LF)(SN) on a label. Note: The products listed above are supplied on embossed-tape.