





REV	DESCRIPTION	DET	DATE
C	UPDATED DRWAING BORDER, 129797C WAS 128640C, ADDED 128487 TO B.O.M.	NDG	02/01/11
D	ITEM 3, 130055 WAS 127191	EL	11/14/11
E	130322CS WAS 127582-1; 130326 WAS 126745; ADDED 508511; ADDED VIEW; ADDED .547 & .375 DIMS	HKS	6/13/13



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 225/245 TOOL, USE ATTACHMENT P/N 119400-1 AND STROKE LIMITER 118362
- 3 FOR USE WITH 2500 TOOL, USE ATTACHMENT P/N 119400-1 AND STROKE LIMITER KIT 119888
- 4 FOR OTHER TOOLS AND/OR OTHER TOOL AND STROKE COMBINATIONS, CONSULT ENGINEERING DEPARTMENT
- 5 SHIP WITH STOP 126747
- 6 SHIP WITH DEFLECTOR 126748-2
- 7 SHIP WITH (2) .030 SHIMS 128290. REFERENCE PB563 FOR PROPER USE.

(E)	PART NO.	QTY	DESCRIPTION	ITEM
	508511	2	B.H.C.S.	10
	128487	1	DRAWBAR	9
	126748-2	1	UNITIZED DEFLECTOR	8
	129797C	1	COLLET	7
(E)	130326	1	GUARD	6
	120095	1	DEFLECTOR	5
	122727	1	BARBED RETAINER	4
	130055	1	UNITIZED CHUCK JAW	3
(E)	130322CS	1	TOP GUARD	2
	127288C	1	ANVIL	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC
42-311: ★ PERMANENT

ITAR/ECCN: EAR99




SCH B#: 8467.99.0190

ENG: NDG CK: DATE: 02/01/11 SCALE: 2:1

HTS: 8467.99.0190

B **99-3763C**

REV	DESCRIPTION	DET	DATE
C	UPDATED DRWAING BORDER, 129797C WAS 128640C, ADDED 128487 TO B.O.M.	NDG	02/01/11
D	ITEM 3, 130055 WAS 127191	EL	11/14/11
E	130322CS WAS 127582-1; 130326 WAS 126745; ADDED 508511; ADDED VIEW; ADDED .547 & .375 DIMS	HKS	6/13/13



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 225/245 TOOL, USE ATTACHMENT P/N 119400-1 AND STROKE LIMITER 118362
- 3 FOR USE WITH 2500 TOOL, USE ATTACHMENT P/N 119400-1 AND STROKE LIMITER KIT 119888
- 4 FOR OTHER TOOLS AND/OR OTHER TOOL AND STROKE COMBINATIONS, CONSULT ENGINEERING DEPARTMENT
- 5 SHIP WITH STOP 126747
- 6 SHIP WITH DEFLECTOR 126748-2
- 7 SHIP WITH (2) .030 SHIMS 128290. REFERENCE PB563 FOR PROPER USE.

(E)	PART NO.	QTY	DESCRIPTION	ITEM
	508511	2	B.H.C.S.	10
	128487	1	DRAWBAR	9
	126748-2	1	UNITIZED DEFLECTOR	8
	129797C	1	COLLET	7
(E)	130326	1	GUARD	6
	120095	1	DEFLECTOR	5
	122727	1	BARBED RETAINER	4
	130055	1	UNITIZED CHUCK JAW	3
(E)	130322CS	1	TOP GUARD	2
	127288C	1	ANVIL	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ PERMANENT	HUCK INTERNATIONAL, INC., I.S.D 1 CORPORATE DR KINGSTON, NEW YORK 12401		
ITAR/ECCN: EAR99	CLEARANCE NOSE ASSEMBLY -07 LGP STRADDLE		
SCH B#: 8467.99.0190	FINAL ASSY: FOR USE WITH 206-375	ENG: NDG	DATE: 02/01/11
HTS: 8467.99.0190	CK:	SCALE: 2:1	
	B	99-3763C	