

REDINGTON COUNTERS, INC.

P.O. Box 608, 130 Addison Road, Windsor, CT 06095

Toll Free: (860) 688-6205 • Fax: 860/688-1591

E-Mail: Info@RedingtonCounters.com • Website: www.RedingtonCounters.com

Item # 1-4635T, Right-hand, top-coming, standard. reset knob, with thumb lever**Right-hand, top-coming, standard. reset knob, with thumb lever**

The 1-4635T is a desk tally version of the Redington Model 1-4635 stroke counter. The counter comes with a thumb lever actuator and can be secured to any flat surface. The 1-4635T is a top coming rotation, with the actuator lever on the right hand side and reset knob located on the left side of the counter. This counter is ideal for counting parts, traffic, or events.

SPECIFICATIONS

Model No.	46
Display	5 Figures, white on black, 0.19 inch (5mm) high
Display Height	0.19 Inch
Display Height	5 mm
No. of Digits	5
Speed	500 counts/minute
Operating Temperature	-15 to +140 °F
Operating Temperature	-25 to +60 °C
Reset Type	Standard knob
Weight	2 oz
Weight	57 gm
Operating Life	Beyond 5 million counts
Rotation	Top-coming
Shaft Extension	Right-hand
Shaft Diameter	0.156 Inch
Shaft Diameter	4.0 mm
Minimum Count Stroke	40 °
Maximum Count Stroke	45 °
Stock Availability	Yes
Mounting Hole Dia.	0.13 x 0.24 Inch

Mounting Hole Dia.	3.3 x 6.1 mm
--------------------	--------------