


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION. BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED. 19

LOC	DIST	P	F	LTR	DESCRIPTION	DATE	APPROVED
CE	16			D	REVISED PER 0A00-0491-00	26JUL00	TA/SB



- 1 FERRULE BODY: BRASS
CAPILLARY: CERAMIC
SPRING, WASHER AND C RING:
STAINLESS STEEL
- 2 FERRULE BODY: NICKEL PLATING
- 3 PRODUCT TO BE BULK PACKAGED
25pcs PER CONTAINER.
- 4 PRODUCT TO BE BULK PACKAGED
100pcs PER CONTAINER.
- 5 DUST COVER INCLUDED, NOT SHOWN.

4	125µm CAPILLARY	501779-6
5 3	125µm CAPILLARY	501779-5
	140µm CAPILLARY	501779-3
	125µm CAPILLARY	501779-1

METRIC	FIBER SIZE	PART NUMBER
--------	------------	-------------

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -	DR B.BRIGGS 3-17-89	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
	CHK D.ERDMAN 3-17-89		
	APPD S.OWENS 3-17-89	NAME FERRULE ASSY WITH SPRING, MULTI-MODE, FIXED SHROUD DUPLEX, OPTIMATE®	
	APPD S.OWENS 3-17-89		
MATERIAL 1	PRODUCT SPEC -	SIZE A	FSCM NO 00779
FINISH 2	APPLICATION SPEC -	DRAWING NO 501779	
	WEIGHT -	SCALE NTS	SHEET 1 OF 1