



TF200AB12

AIN Flanged Termination

Power: 200 Watts (CW)

Resistance: $50 \Omega \pm 5\%$


VSWR: 1.20:1

Frequency Range: DC to 2.5 GHz

Substrate: AIN



TYPICAL PERFORMANCE RETURN LOSS



For detailed information regarding this product or sample request contact Johanson Sales




Johanson Manufacturing Corporation • 301 Rockaway Valley Road, Boonton, New Jersey 07005 • Phone 973.334.2676 • Fax 973.334.2954
STAY TUNED • ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION • WWW.JOHANSONMFG.COM

Nov 08



TF200AB12

AIN Flanged Termination



For detailed information regarding this product or sample request contact Johanson Sales



Johanson Manufacturing Corporation • 301 Rockaway Valley Road, Boonton, New Jersey 07005 • Phone 973.334.2676 • Fax 973.334.2954
STAY TUNED • ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION • WWW.JOHANSONMFG.COM

Nov 08