



► ISORYL screwdrivers for Pozidriv® heads

AD For Pozidriv® heads

- High-strength alloy steel blade.
- Burnished finish.


| ⇒ | Pozidriv® no. | Ø1 x L1 mm | Ø2 x L2 mm | L mm | ΔΔ g |
|-----------------|---------------|------------|------------|------|------|
| AD.0X50 | PZ.0 | 4 x 50 | 20,5 x 80 | 130 | 31 |
| AD.1X75 | PZ.1 | 4 x 75 | 24 x 90 | 165 | 55 |
| AD.2X100 | PZ.2 | 6 x 100 | 28 x 100 | 200 | 77 |
| AD.2X125 | PZ.2 | 6 x 125 | 28 x 100 | 225 | 81 |
| AD.3X150 | PZ.3 | 8 x 150 | 30 x 110 | 260 | 142 |



ADB For Pozidriv® heads - short blades

- For use in confined spaces.
- Burnished finish.

| ⇒ | Pozidriv® no. | Ø1 x L1 mm | Ø2 x L2 mm | L mm | ΔΔ g |
|-----------------|---------------|------------|------------|------|------|
| ADB.1X40 | PZ.1 | 5 x 40 | 29 x 50 | 90 | 38 |
| ADB.2X40 | PZ.2 | 6 x 40 | 29 x 50 | 90 | 44 |





► ISORYL screwdrivers for Phillips® heads

AP For Phillips® heads

- Chrome finish.

| ⇒ | Phillips® no. | Ø1 x L1 mm | Ø2 x L2 mm | L mm | ΔΔ g |
|-----------------|---------------|------------|------------|------|------|
| AP.0X50 | PH.0 | 4 x 50 | 20,5 x 80 | 130 | 31 |
| AP.0X75 | PH.0 | 4 x 75 | 20,5 x 80 | 155 | 33 |
| AP.1X75 | PH.1 | 5 x 75 | 24 x 90 | 165 | 55 |
| AP.1X100 | PH.1 | 5 x 100 | 24 x 90 | 190 | 59 |
| AP.2X100 | PH.2 | 6 x 100 | 28 x 100 | 200 | 77 |
| AP.2X125 | PH.2 | 6 x 125 | 28 x 100 | 225 | 81 |
| AP.3X150 | PH.3 | 8 x 150 | 30 x 110 | 260 | 142 |
| AP.4X200 | PH.4 | 10 x 200 | 34 x 120 | 320 | 246 |



APB For Phillips® heads - short blades

- For use in confined spaces.
- Chrome finish.

| ⇒ | Phillips® no. | Ø1 x L1 mm | Ø2 x L2 mm | L mm | ΔΔ g |
|-----------------|---------------|------------|------------|------|------|
| APB.0X40 | PH.0 | 4 x 40 | 29 x 50 | 90 | 33 |
| APB.1X40 | PH.1 | 5 x 40 | 29 x 50 | 90 | 36 |
| APB.2X40 | PH.2 | 6 x 40 | 29 x 50 | 90 | 40 |

