







8767207S
(ON 0NIMVHD) 品名図

版数 REV.	年月日 DATE	DGN NO.	変更内容 DESCRIPTION	製図 DR.	担当 CHK.	査閲 APPD.	承認 APPD.
2	20.Nov.1989	25942	REDRAWN				
3	8.Sep.2003	053208	CHANGED TO BILINGUAL etc.	M.TANAKA	S.HARA	T. Ichimori	K. Takeda



NOTE1. APPLICABLE MATING PIN: □0.64 $\pm$ 0.05

2. APPLICABLE WIRE: AWG#18~#22(0.85~0.3mm²)
INSULATION OUTER DIA.: ϕ 1.4~ ϕ 2.4

3. NO PLATING ON THE SHEARED EDGES OF CONTACT.

4. PART NUMBER & QUANTITY AS INDICATED. (COLOR:ORANGE)

△ 5. REFER TO "JABL-1309(-E)" FOR COMPLETE CRIMP AND WIRE SPECIFICATIONS.

注1. 挿入ピンは板厚□0.64 $\pm$ 0.05とする。

△ 2. 使用電線は、AWG#22~#18(0.3~0.85mm²)相当、
被覆外径 ϕ 1.4~ ϕ 2.4の撚線とする。

3. 剪断面にめっきは付かない。

△ 4. 図示の如く品名及び数量を表示する。(文字色相:オレンジ色)

△ 5. 圧着状態、適用電線については "JABL-1309(-E)" を参照のこと。

3	SOCKET CONTACT	5000	PHOSPHOR BRONZE	TIN PLATING	
2	PAPER TAPE	1	PAPER		
1	MAGAGINE	1	PAPER		
符号 NO.	名 DESCRIPTION	個数 QTY.	材 料 MATERIAL	仕 上 FINISH	備 考 REMARKS
仕様書 (SPECIFICATION)			第1版 (ORIGINAL DATE)	尺 寸 (SCALE)	製 図 (SERIES)
JACS-1309 △			29.Feb.1988	1:5 △	IL-A05 △
公差 (GENERAL TOLERANCE)			製図 DR.	名称 (TITLE)	
寸法 (DIMENSION)			担当 CHK.	IL-A05-C1-5000	
角度 (ANGLES)			査閲 APPD.	(MAGAGINE ASSEMBLY)	
. $\pm$ 0.3			承認 APPD.	重量 (WEIGHT)	
.X $\pm$ 0.3				JAE CONNECTOR.COM	
.XX $\pm$ 0.2				JAE	
.XXX $\pm$				JAE	
				図面番号 (DRAWING NO.)	
				SJ022948	
				版数 (REV.)	
				3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[IL-AG5-C1-5000](#)