




## SANDVIK BELZER

## Diagonal cutters

Produced by high performance ball-bearing steel, numerically controlled machine grinding guarantees edge angle accuracy and contact which increases tool reliability and consistency. Precision induction hardened edges, 63-65 HRC.  
Handles with return spring.

## Oval head



## 2646M - 2649



| Product code    | EAN code<br>731415+ |   | A<br>mm | B<br>mm | C<br>mm | D<br>mm | F<br>mm | Capacity<br>mm | Bevel |    |
|-----------------|---------------------|---|---------|---------|---------|---------|---------|----------------|-------|----|
| <b>2646M</b>    | 1487928             | 1 | 108     | 8       | 8       | 5       | 0,8     | 0,1-0,8        | Ultra | 44 |
| <b>2646R</b>    | 1304706             | 1 | 110     | 10      | 10      | 6       | 0,8     | 0,2-1,25       | Micro | 46 |
| <b>2646RK *</b> | 1496678             | 1 | 110     | 10      | 10      | 6       | 0,8     | 0,2-1,25       | Micro | 46 |
| <b>2646RA</b>   | 1834838             | 1 | 110     | 10      | 10      | 6       | 0,8     | 0,1-1,0        | Ultra | 46 |
| <b>2666</b>     | 0058006             | 1 | 112,5   | 12,5    | 12,5    | 6       | 1,2     | 0,3-1,6        | Micro | 50 |
| <b>2649</b>     | 0058013             | 1 | 125     | 16      | 16      | 8       | 1,6     | 0,4-2,0        | Micro | 88 |

## Tapered head

## 2646 - 2648A



| Product code     | EAN code<br>731415+ |   | A<br>mm | B<br>mm | C<br>mm | D<br>mm | F<br>mm | Capacity<br>mm | Bevel |    |
|------------------|---------------------|---|---------|---------|---------|---------|---------|----------------|-------|----|
| <b>2646</b>      | 1304638             | 1 | 110     | 10      | 10      | 6       | 0,8     | 0,2-1,25       | Micro | 46 |
| <b>2646K *</b>   | 1495862             | 1 | 110     | 10      | 10      | 6       | 0,8     | 0,2-1,25       | Micro | 46 |
| <b>2646A</b>     | 1304645             | 1 | 110     | 10      | 10      | 6       | 0,8     | 0,1-1,0        | Ultra | 46 |
| <b>2646AK *</b>  | 1396619             | 1 | 110     | 10      | 10      | 6       | 0,8     | 0,1-1,0        | Ultra | 46 |
| <b>2666FK</b>    | 1066079             | 1 | 112,5   | 12,5    | 12,5    | 6       | 1,2     | 0,2-1,25       | Ultra | 49 |
| <b>2666FKK *</b> | 1496593             | 1 | 112,5   | 12,5    | 12,5    | 6       | 1,2     | 0,2-1,25       | Ultra | 49 |
| <b>2648 *</b>    | 1304713             | 1 | 125     | 16      | 16      | 8       | 1,6     | 0,4-2,0        | Micro | 88 |
| <b>2648A</b>     | 1304720             | 1 | 125     | 16      | 16      | 8       | 1,6     | 0,3-1,6        | Ultra | 88 |

\* with leadcatcher