


REV. X

NOTES:

- CONTACT RETENTION FORCE: 2 lbs
- MAX ALLOWABLE BOW: .006 [.15] IN/IN
- "END WALLS" AFTER CUTTING SHOULD BE $.015 \pm .001$ $.005$ $.38 \pm .03$ $.005$ $.13$.
- WHEN FILLING THE ASSEMBLY, ALL CONTACTS MUST BE FACING THE SAME DIRECTION.
- ($\odot$) REPRESENTS CRITICAL DIMENSION.
- CUT FLASH: .015 [.38] MAX WITH NO FLASH ALLOW IN HOLES.
- .003 [.08] MAX TERMINAL BURR.

Do not scale
from this print

UNLESS OTHERWISE NOTED
 DIMENSIONS ARE IN INCHES
 TOLERANCES ARE:
 ONE PLACE DECIMALS $\pm .1$ [.3] THREE PLACE DECIMALS $\pm .005$ [.13]
 TWO PLACE DECIMALS $\pm .01$ [.3] FOUR PLACE DECIMALS $\pm .0020$ [.051]
 ANGLES $\pm 2^\circ$

TITLE:
CLOSED ENTRY
SOCKET STRIPDWG NO:
CES-1XX-XX-X-X-XX
SHEET 1 of 1

CES-1XX-XX-X-X-XX


POSITION SPECIFICATIONS
-01 THRU -50CONTACT LEAD STYLE
-01: "A"=.128 [3.25] (USE C-45-01-X)
-02: "A"=.223 [5.66] (USE C-45-02-X)OPTIONS
-RA: RIGHT ANGLE
(STYLE -02 ONLY)ROW SPECIFICATION
-S: SINGLE
(USE CES-XX-S)

PLATING SPECIFICATIONS

-T: TIN - SPECIFY -T IN CONTACT SUFFIX -X
 -G: GOLD - SPECIFY -G IN CONTACT SUFFIX -X
 -S: SELECTIVE - SPECIFY -S IN CONTACT SUFFIX -X
 -F: FLASH GOLD - SPECIFY -F IN CONTACT SUFFIX -X
 (AVAILABLE IN -01 LEAD STYLE ONLY)
 -L: LIGHT SELECTIVE - SPECIFY -L IN CONTACT SUFFIX -X

PT-1-24-01-53

NOTE:
PINS TO ALL BE FACING
THE SAME DIRECTION

PACKAGING VIEW LEAD STYLE -01 & -02
SCALE: .75PACKAGING VIEW LEAD STYLE -02-RA
SCALE: .75

PACKAGING TABLE (5 POS MIN)		
LEAD STYLE	TUBE	PLUG
-01 & -02	PT-1-24-01-53	TP-24 (2)
-02-RA	PT-1-24-03-78	TP-09 (2)

MATERIAL:
GLASS FILLED POLYESTER
COLOR: BLACKTERMINAL:
PHOS BRONZE

santec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-6733 P.O. BOX 1147
 CODE 55322

MADE BY:
KOLB 12-6-89CES-1XX-XX-X-X-XX
SHEET 1 of 1

PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SANTEC INC. AND SHALL NOT BE
 REPRODUCED OR TRANSMITTED IN
 ANY FORM OR BY ANY MEANS
 WITHOUT THE WRITTEN CONSENT OF SANTEC INC.