

Catalog Number: LTC0381000
Product ID: 7TAD012620R0001
UPC Number: 78621032378
Status: Active



Actual

Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/8 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings, 1,000 Foot Reel

- Fast installation, even in tight or cramped spaces.
- Smooth inner diameter allows easy wire pulling.
- Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.
- Lightweight and liquidtight.
- UL Listed for direct burial



Actual

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	T&B
Type	Liquidtight Flexible Non-Metallic Conduit
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily
Application	Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles.
Standard	UL E95745, CSA
Trade Size	3/8 Inch/16mm
Outside Diameter	18.0mm
Inside Diameter	12.3mm
Length	1,000 Feet
Voltage Rating	600 Volts
Material	PVC
Color	Black

European Specifications (ETIM)

ETIM	EC001177 Protective plastic hose
Nominal size in inch	3/8 inch
Material	PVC
Operating temperature	-18-+105°C
Flexibility	Flexible
Colour	Black
Approved according to CSA	Y

Packaging

Outer Quantity	1000
Weight Uom	12.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US [Available on Website](#)

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.

T&B Technical Support
MS 3B-50

Hours: 7AM - 6PM CDT
Monday-Friday

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com