








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		ECR-16-015436	NOV11	N.L	D.Z



SECTION B-B
SCALE 20:1




SECTION C-C
SCALE 20:1



SECTION A-A
SCALE 20:1

2.06	.081	-	-
2.01	.079	-	-
1.93	.076	-	-
1.91	.075	-	-
1.57	.062	16.76	.660
1.52	.060	2.67	.105
1.40	.055	2.41	.095
1.37	.054	2.29	.090
0.20	.008	2.16	.085
0.13	.005	2.08	.082
MM	IN	MM	IN
CONVERSION TABLE			



PRE-TIN	0.20 BRASS	1.52 MAX	30-24(0.05-0.2mm)	794046-1
FINISH	MATERIALE	INSULATION DIAMETER	WIRE RANGE	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 8-1-94	TE Connectivity	
		CHK R. SWING 8-1-94		
DIMENSIONS: INCHES		APVD C. CASH 8-4-94	NAME	
		PRODUCT SPEC	.062 SOCKET COMMERCIAL PIN & SOCKET -	
		108-1037		
		APPLICATION SPEC		
		30-114-1013		
MATERIAL SEE TABLE		FINISH SEE TABLE	WEIGHT 0	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE N/A	SHEET 1 OF 1