




LOC		DIST		REVISIONS			
-		-		REV	DESCRIPTION	DATE	OWN
-		-		K	REV PER ECO 11-025643	2-7-12	CT
-		-					
-		-					
-		-					

THIS AREA SOLDER DIPPED. SOLDER TAIL DIMENSIONS APPLY PRIOR TO SOLDER DIP.
SOLDER IS RoHS COMPLIANT Sn.
3. CHARACTERISTIC IMPEDANCE: 100 OHMS NOMINAL

37.49 [1.476]	7.06 [.278]	8.25 [.325]	30.25 [1.191]	SAME AS 1445626-9 EXCEPT TAILS ARE SOLDER DIPPED	1-1445626-0
37.49 [1.476]	7.06 [.278]	8.25 [.325]	30.25 [1.191]	SAME AS 1445626-1 EXCEPT WITH .278 SOLDER TAIL LENGTH	1445626-9
39.95 [1.573]	9.52 [.375]	10.72 [.422]	33.50 [1.319]	SAME AS 1445626-2 EXCEPT TAILS ARE SOLDER DIPPED	1445626-8
35.84 [1.411]	5.41 [.213]	5.79 [.228]	28.58 [1.125]	SAME AS 1445626-1 EXCEPT TAILS ARE SOLDER DIPPED	1445626-6
36.78 [1.448]	6.35 [.250]	7.54 [.297]	30.33 [1.194]	SAME AS 1445626-4 EXCEPT TAILS ARE SOLDER DIPPED	1445626-5
36.78 [1.448]	6.35 [.250]	7.54 [.297]	30.33 [1.194]	SAME AS 1445626-1 EXCEPT WITH .250 SOLDER TAIL LENGTH	1445626-4
34.65 [1.364]	4.2 [.166]	4.60 [.181]	27.38 [1.078]	SAME AS 1445626-1 EXCEPT WITH .166 SOLDER TAIL LENGTH	1445626-3
39.95 [1.573]	9.52 [.375]	10.72 [.422]	33.50 [1.319]	SAME AS 1445626-1 EXCEPT WITH .375 SOLDER TAIL LENGTH	1445626-2
35.84 [1.411]	5.41 [.213]	5.79 [.228]	28.58 [1.125]	PER ARINC 664 STANDARD;	1445626-1
V REF	U REF	T REF	S REF	DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN Brent D. Yohn 7JAN2004	TE Connectivity	
DIMENSIONS: mm [INCH]		CHK W.H. BERNHART 7JAN2004	NAME ASSEMBLY, PIN, QUADRAX, 2mm SQ, FRONT RELEASE-FRONT REMOVABLE, ADN, WITH PIN CONTACTS	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W.H. BERNHART 7JAN2004	SIZE A1	
9 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		PRODUCT SPEC APPLICATION SPEC 114-13123 WEIGHT CUSTOMER DRAWING	RESTRICTED TO A100779C-1445626 SCALE 3:2	