





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	'A'	'B'	'C'	WEIGHT grams/100 pcs
THMSC36H07	36.0	9.0	13.4	77



NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. APPLICATION SPECIFICATION:
HOLE DIAMETER: 6.3 - 7.1 mm
PANEL THICKNESS: 0.8 - 7.0 mm
3. MATERIAL:
-30: BLACK HEAT STABILIZED NYLON 6/6
-39: NATURAL HEAT STABILIZED NYLON 6/6



ALL DIMENSIONS ARE METRIC [mm]

CAD FILENAME/LAYERS

G03597DC_DC_GB0239NK/00B

PANDUIT CORP.

TINLEY PARK, ILLINOIS

THMSC36H07
TIE HARNESS MOUNT

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE METRIC
TOLERANCE: $\pm 0.5\text{mm}$

[illegible]