

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

G


DIST

14

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	K	REV PER 0G3A-0765-02	19DEC02	JR	TM

AMP WIRE RANGE	FILE E13288	LR7189 Certified
8 AWG STRANDED	8 AWG STRANDED	8 AWG STRANDED



A

52262

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
90 °C

VOLTAGE RATING:
600V MAX

CIRCULAR MIL AREA:
6.64-10.5mm² [13,100-20,800]
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.20 [.008]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH		

MATERIAL

COPPER ASTM B-152

FINISH

TIN PLATE

DWN

JR RUTH

19DEC02

CHK

R. HERSEY

19DEC02

APVD

T. MICHIELUTTI

19DEC02

PRODUCT SPEC

NOT AVAILABLE

APPLICATION SPEC

NOT AVAILABLE

WEIGHT

-

CUSTOMER DRAWING

NAME

TERMINAL, RING TONGUE,
-
-

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=52262

RESTRICTED TO

-

SCALE

1:1

SHEET

1

OF

1

REV

K

500

ON TAPE & REEL

2-52262-1

100

LOOSE PIECE

52262-1

QTY

PACKAGE TYPE

PART NO

AMP 1471-9 REV 31MAR2000