




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART#	COLOR	DESCRIPTION	WEIGHT*
CJS6X88TGY CJS6X88TGRDY CJS6X88TGBUY CJS6X88TGGRY CJS6X88TGVLY CJS6X88TGYLY	BLACK RED BLUE GREEN VIOLET YELLOW	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. WIRE CAP LABEL IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.314 LB/100 PCS (1503g/100 PCS)

*WEIGHT IS APPROXIMATE

NOTES:

1. BLUE WIRE CAP DESIGNATES CATEGORY 6A PERFORMANCE.
2. MATERIAL:
MODULE HOUSING- ABS
MODULE SHIELD- TIN PLATED PHOS. BRONZE.
WIRE CAP/CLIP - ZINC AND PC
3. ALL CATEGORY 6A, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. .187 x .010" GROUNDING TAB PROVIDED AS OPTIONAL CONDUCTIVE PATH FOR GROUNDING.



ACTUAL SIZE

PART NUMBER		CJS6X88TG**Y	
TITLE		TX6A 10GIG SHIELDED JACK MODULE	
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479NU/06	
DATASET FILE NAME		M02479NU_DC359/06A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ± .03 [.8]		SEE NOTE 2	
.XXX ± .010 [.3]		DRAWING NUMBER:	
ANGLES ±		02479-359	
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
AFW	3-11-06	NGM	FULL
SHT 1 OF 1		SIZE	
A			