




EPIC® Rectangular Connectors



HBE 48 Housings: Single Lever on Base


HOODS

TOP ENTRY



All dimensions are in mm.

SIDE ENTRY







Specifications: DIN 43652
Temperature Range: -40°C to +125°C

Protection class: NEMA 4, NEMA 12, IP65
Material: Aluminum alloy, powder coated

Position of Cable Entry	Size of Entry			Part Numbers			Complete your installation with a SKINTOP®, Pg 352			
	PG	NPT	Metric	PG	NPT	Metric	PG- Nylon	PG- Metal	Metric- Nylon	Metric- Metal
Top Entry	29	1"	32	10155000	101550NP	19155000	53015160	52015760	53111040	53111040
	36	1 1/4"	40	10156000	101560NP	19156000	53015170	52015765	53111050	53112050
	42	-	50	10157000	-	19157000	53015180	52015766	53111060	53112060
Side Entry	29	1"	32	10158000	101580NP	19158000	53015160	52015760	53111040	53111040
	36	1 1/4"	40	10159000	101590NP	19159000	53015170	52015765	53111050	53112050
	42	-	50	10160000	-	19160000	53015180	52015766	53111060	53112060

Metric hoods do not come with a neck.


PANEL MOUNT BASES



Specifications: DIN 43652
Temperature Range: -40°C to +125°C
Protection class: NEMA 4, NEMA 12, IP65
Material: Aluminum alloy, powder coated

Without Dust Cover	With Dust Cover with hold down screw and no dust cover bolts	With Dust Cover with hold down screw and dust cover bolts
10161000	10152000	10152500

SURFACE MOUNT BASES



Specifications: DIN 43652
Temperature Range: -40°C to +125°C

Protection class: NEMA 4, NEMA 12, IP65
Material: Aluminum alloy, powder coated

All dimensions are in mm.

# of Entries	Size of Entry			Part Numbers			Complete your installation with a SKINTOP®, Pg 352			
	PG	NPT	Metric	PG	NPT	Metric	PG- Nylon	PG- Metal	Metric- Nylon	Metric- Plastic
2 Entries	29	1"	32	10166000	101660NP	19166000	53015160	52015760	53111040	53112040
	36	1 1/4"	40	10166100	101661NP	19166100	53015170	52015765	53111050	53112050
1 Entry	29	1"	32	10165000	101650NP	19165000	53015160	52015760	53111040	53112040
	36	1 1/4"	40	10165100	101651NP	19165100	53015170	52015765	53111050	53112050
2 Entries w/ dust cover	29	1"	32	10168000	101680NP	19168000	53015160	52015760	53111040	53112040
	36	1 1/4"	40	10168100	101681NP	19168100	53015170	52015765	53111050	53112050
1 Entry with dust cover	29	1"	32	10167000	101670NP	19167000	53015160	52015760	53111040	53112040
	36	1 1/4"	40	10167100	101671NP	19167100	53015170	52015765	53111050	53112050