



APC Displays+
01480 226600
sales@apc-displays.co.uk

5.7" Open Frame

Part No : HE057AOT4
Item Description : 5.7" monitor / 4 wire resistive touch

Advantage and Application

- long term availability of adopted TFT LCD panels (stability of supply for min. 3 years)
- Analog RGB / DVI supportable
- 4 wire resistive touch adopted
- RS232 communication (option)
- Fine finishing metal chassis (brilliant design & complete set level OSD button)
- Application
 - Kiosks
 - ATMs
 - Casino & Amusement games
 - Lottery and Ticket sales
 - Self-Services
 - Industrial process control

Item	Description
Frame / bezel Color	EGL in black
Display Type	Size: 5.7" diagonal, Type: Active matrix TFT LCD Aspect ratio: 4 x 3
Active area	115.2 (H) x 86.4 (V)
Optimal (native) resolution	640 x 480
Support color	262K colors
Brightness (without touch)	700 cd/m2
Viewing Angles	80 / 80 / 70 / 70
Input video supportable	Analog RGB, DVI, Audio (option, 2W x 2W)
Temperature	Operating ; - 30°C ~ +85 °C Storage : - 30°C ~ +85 °C
Mounting Holes	VESA / 75 x 75 mm
Applicable Graphic Mode	VESA standard timing control
Weight & Volume	Unit Weight : 1,017 g, Carton Packing : pcs Carton weight : Kg

