



Dimensions

DIN 965


BS 4183

ISO 7046

Materials / Finishes:

Stainless steel / Self colour

Other materials and finishes available on request



d	M2	M2.5	M3	M3.5	M4	M5	M6	M8
H max (BS / DIN)	1.2	1.5	1.65	1.93	2.2	2.5	3	4.5
H max (ISO)	1.2	1.6	1.65	2.35	2.7	2.7	3.3	4.65
recess (BS / DIN)	1	1	1	2	2	2	3	4
recess (ISO)	0	1	1	2	2	2	3	4
D nom (BS)	-	5.5	6.3	7.35	8.4	10	12	16
D nom (DIN)	3.8	4.7	5.6	6.5	7.5	9.2	11	14.5
D nom (ISO)	3.8	4.7	5.5	7.3	8.4	9.3	11.3	15.8

NB: Generally our preferred stock is to DIN - if dimensions are critical to your application you should check with us prior to ordering.

Preferred sizes - Stainless steel

d	M2	M2.5	M3	M3.5	M4	M5	M6	M8
L 6								
8								
10								
12								
16								
20								
25								
30								
35								
40								
45								
50								
60								
65								
70								

Non Preferred
Please enquire