



English

[Webshop](#) [Contact](#) [Sitemap](#) [Find Product](#)

- Home
- Kvaser
- Products
 - CAN
 - USB**
 - Data Logger
 - Rugged
 - PCMCIA
 - Wireless
 - PCI
 - ISA
- LIN
- Cables
- Product List
- Find Product
- MagiSync
- Representatives
- Software Tools
- About CAN
- Developer
- Education
- Support
- Downloads
- Press Room

Home ▶ Products ▶ CAN ▶ USB ▶ Kvaser Leaf Light HS

Kvaser Leaf Light HS



Product description

EAN Number: 73-30130-00241-8

The Kvaser Leaf Light supports full speed USB interface for CAN with high performance at a low cost. Kvaser Leaf Light is a reliable low cost product. Loss free transmission and reception of standard and extended CAN messages on the CAN bus is transmitted with a time stamp precision of 100 microseconds.

Description	Technical Specification	Downloads	Additional Images
Property		Value	
Galvanic Isolation	No		
Bitrate	5-1000 kbit/s		
Silent mode	No		
Error frame generation	No		
Error frame detection	Yes		
Weight	100 g		
Timestamp resolution	100		
On board buffer	Yes		
Maximum message rate, send	8000		
Maximum message rate, receive	8000		
Sound	No		
Clock synchronization	N/A		
Dimensions (WxLxH)	25x100x20 mm (1.0x3.9x0.8in.)		
The information herein is subject to change without notice.			