


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.






| PART NUMBER   | SEE<br>DETAIL | "A" +/- .062 | "B"          | MARKER<br>ACROSS | TUBING<br>COLOR | SEE<br>STYLE | MARKERS<br>PER ROLL |
|---------------|---------------|--------------|--------------|------------------|-----------------|--------------|---------------------|
| H050X034H1T   | A             | 0.50 [12.70] | 0.75 [19.05] | 4                | WHITE           | A            | 2000                |
| H075X034H1T   | B             | 0.75 [19.05] | 1.00 [25.40] | 2                |                 |              | 1000                |
| H100X034H1T   | C             | 1.00 [25.40] | 0.75 [19.05] | 2                |                 |              | 1000                |
| H150X034H1T   | D             | 1.50 [38.10] | 1.00 [25.40] | 1                |                 |              | 500                 |
| H200X034H1T   | E             | 2.00 [50.80] | 0.75 [19.05] | 1                |                 |              | 500                 |
| H050X034H2T   | A             | 0.50 [12.70] | 0.75 [19.05] | 4                | YELLOW          | A            | 2000                |
| H075X034H2T   | B             | 0.75 [19.05] | 1.00 [25.40] | 2                |                 |              | 1000                |
| H100X034H2T   | C             | 1.00 [25.40] | 0.75 [19.05] | 2                |                 |              | 1000                |
| H150X034H2T   | D             | 1.50 [38.10] | 1.00 [25.40] | 1                |                 |              | 500                 |
| H200X034H2T   | E             | 2.00 [50.80] | 0.75 [19.05] | 1                |                 |              | 500                 |
| H050X034H3T   | A             | 0.50 [12.70] | 0.75 [19.05] | 4                | BLACK           | A            | 2000                |
| H075X034H3T   | B             | 0.75 [19.05] | 1.00 [25.40] | 2                |                 |              | 1000                |
| H100X034H3T   | C             | 1.00 [25.40] | 0.75 [19.05] | 2                |                 |              | 1000                |
| H150X034H3T   | D             | 1.50 [38.10] | 1.00 [25.40] | 1                |                 |              | 500                 |
| H200X034H3T   | E             | 2.00 [50.80] | 0.75 [19.05] | 1                |                 |              | 500                 |
| H050X034H4T   | A             | 0.50 [12.70] | 0.75 [19.05] | 4                | RED             | A            | 2000                |
| H075X034H4T   | B             | 0.75 [19.05] | 1.00 [25.40] | 2                |                 |              | 1000                |
| H100X034H4T   | C             | 1.00 [25.40] | 0.75 [19.05] | 2                |                 |              | 1000                |
| H150X034H4T   | D             | 1.50 [38.10] | 1.00 [25.40] | 1                |                 |              | 500                 |
| H200X034H4T   | E             | 2.00 [50.80] | 0.75 [19.05] | 1                |                 |              | 500                 |
| H050X034H1T-B | A             | 0.50 [12.70] | 0.75 [19.05] | 4                | WHITE           | B            | 10000               |
| H075X034H1T-B | B             | 0.75 [19.05] | 1.00 [25.40] | 2                |                 |              | 5000                |
| H100X034H1T-B | C             | 1.00 [25.40] | 0.75 [19.05] | 2                |                 |              | 5000                |
| H150X034H1T-B | D             | 1.50 [38.10] | 1.00 [25.40] | 1                |                 |              | 2500                |
| H200X034H1T-B | E             | 2.00 [50.80] | 0.75 [19.05] | 1                |                 |              | 2500                |

8




NOTES:  
1. DIMENSIONS IN [ ]  
ARE IN MILLIMETERS.

STYLE A



STYLE B



| REV | DATE    | BY  | CHK  | APR  | DESCRIPTION                                                                                                                                                                                    | ECN        |
|-----|---------|-----|------|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|
| 8   | 4/29/15 | RVU | SEWH | JHAC | ADD NEW COLUMN OF MARKERS PER ROLL.                                                                                                                                                            | GAECN02784 |
| 7   | 1/20/15 | RVU | SEWH | MSAD | REVISE OLD LOGO TO CURRENT PANDUIT LOGO.                                                                                                                                                       | GAECN02540 |
| 6   | 4/12/12 | RVU |      |      | REVISED H150 PARTS TO SHOW ALL MARKERS ARE ONLY 1.5" LONG.                                                                                                                                     | 6731       |
| 5   | 5/21/09 | RVU |      |      | +/- .12, +/- .062, +/- .020 WAS +/- .03, +/- .032, +/- .010. HT: .25 +/- .032 WAS .250. MAT'L. HSK TUBING GUMHS31, 3.5 WIDE LINER WAS GUMHS. ADD "A" +/- .062. ADD STYLE B. VIEW FOR BULK BOX. | 5593       |

|                                                                      |        |      |                                                                                                 |            |  |
|----------------------------------------------------------------------|--------|------|-------------------------------------------------------------------------------------------------|------------|--|
| TITLE                                                                |        |      | H***X034H**<br>OPTIMUM COMPUTER PRINTABLE MIL. SPEC.<br>HEAT SHRINK MARKERS<br>CUSTOMER DRAWING |            |  |
| ITEM REVISION NAME                                                   |        |      | 100923NJ/11                                                                                     |            |  |
| DATASET FILE NAME                                                    |        |      | 100923NJ_DC_C10433/11J                                                                          |            |  |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ] |        |      | .x ± .12 [ 3.05 ]      .xxx ± .020 [ 0.508 ]<br>.xx ± .062 [ 1.57 ]      ANGLES ±               |            |  |
| THIRD ANGLE<br>PROJECTION                                            |        |      | MATERIAL:<br>HEATSHRINK<br>TUBING GUMHS31,<br>3.5 WIDE LINER<br>DRAWING NUMBER:<br>C10433       |            |  |
| DRAWN BY                                                             | DATE   | CHK  | SCALE                                                                                           | SIZE       |  |
| RVU                                                                  | 8/1/06 | MSAD | NTS                                                                                             | SHT 1 OF 1 |  |