







High Density D-Sub Connector

156-2215, 156-2026

KOBICONN

High Density D-Sub Connector



Dimensions: mm (in.)

SPECIFICATIONS	
Insulator:	Glass filled PBT
Shell:	Cold rolled steel
Contact:	Brass (male) - Contact Stock No.:156-2000
Current rating:	1 amp per contact
Breakdown voltage:	1000V
Temperature rating:	-55°C to +105°C
Contacts:	Gold flashed

Housing Part No.	Pins	A	B	C	D	E	F
156-2215	15	30.80 (1.213)	25 (.984)	16.92 (.666)	8.3 (.327)	12.6 (.496)	5.9 (.232)
156-2026	26	39.20 (1.213)	33.32 (1.312)	25.25 (.994)	8.3 (.327)	12.6 (.496)	5.9 (.232)

Date Last Revised: 6/21/12

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300020

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

156-2215, 156-2026

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[156-2026](#) [156-2215](#)