



Sample photo

Order symbol: PCM 200/175 XT
Product nbr: 6015929
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074038418
El. number:
Finland: 3421629
Electric No. Denmark: 8212027417
Electric No. Sweden: 2535463

Including: Base with metric knock-outs and PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
Length	Width	Height			
mm:	255	180	175	MIN 15	DIN-15 Mounting rail
inch:	10.0	7.1	6.9	MIN 20	DIN-15 Mounting rail
Materials:				MIV 15	DIN-35 Mounting rail
Material:	Polycarbonate			MIV 20	DIN-35 Mounting rail
Base colour:	RAL 7035 -light grey			FP A 200/180	Front plate (Aluminium)
Cover screws material:	Polyamide			HFP 180	Front plate hinge series
Cover colour:	Smoked grey			FP 22046	Wall fastening lug (4 pcs)
Cover screws colour:	Black			Rating:	
Gasket material:	Polyurethane			Ingress Protection (EN 60529): IP66/67	
Temperatures:				Impact Resistance (EN 62262): IK08	
Temperature °C (short term):	-40 ... 120 °C			Electrical insulation: Totally insulated	
Temperature °C (continuous):	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (short term):	-40 ... 250 °F			UV resistance: UL 508	
Temperature °F (continuous):	-40 ... 175 °F			Flammability Rating: UL 746C 5V	
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960	
MIV 200	Mounting plate (Galvanized steel)			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
				Certificates:	
				Germanischer Lloyd (GL)	
				SGS Fimko	
				Gost R	

