


Specification and Ordering Information for 3M™ BBI-A Series Bus Bar Tubing

Product Number	UPC (051135-)	Outside Dimension (Bar Circumference A)	Rectangular	Square	Round (Diameter)	Case Qty.
						
5, 8 & 15 kVBus Bar Size Ranges						
BBI-3A	35726 35727	3.28–5.57" (83–141 mm)	1 1/2 x 1/4–2 1/2 x 1/2" (38 x 6–64 x 13 mm)	1 x 1–1 1/2 x 1 1/2" (25 x 25–38 x 38 mm)	1 1/8–1 3/4" (29–44 mm)	20 50
BBI-4A	35728 35729	5.43–8.86" (138–225 mm)	2 1/2 x 3/8–4 x 3/4" (64 x 10–102 x 19 mm)	2 x 2" (51 x 51 mm)	1 3/4–2 3/4" (44–70 mm)	20 50
BBI-5A	35730 35731	6.67–10.86" (169–276 mm)	3 x 5/8–5 x 3/4" (76 x 16–127 x 19 mm)	2 x 2–2 x 1/2 x 2 1/2" (51 x 51–64 x 64 mm)	2 1/8–3 3/8" (54–86 mm)	20 50
BBI-6A	35732 35733	7.57–12.86" (192–327 mm)	3 1/2 x 1/2–6 x 3/4" (89 x 13–152 x 19 mm)	2 1/2 x 2 1/2–3 x 3" (64 x 64–76 x 76 mm)	2 1/2–4" (64–102 mm)	20 50
BBI-7A	35734 35735	8.28–13.00" (210–330 mm)	4 x 1/4–6 x 3/4" (102 x 6–152 x 19 mm)	2 1/2 x 2 1/2–3 x 3" (64 x 64–76 x 76 mm)	2 3/4–4 1/8" (70–105 mm)	20 50
BBI-8A	35736 35737	10.29–16.43" (261–417 mm)	5 x 1/4–8 x 3/8" (127 x 6–203 x 10 mm)	3 x 3–4 x 4" (76 x 76–102 x 102 mm)	3 3/8–5 1/8" (86–130 mm)	20 50
BBI-9A	35876 35877	12.29–19.23" (312–488 mm)	6 x 1/4–9 x 3/4" (152 x 6–229 x 19 mm)	3 1/2 x 3 1/2–5 x 5" (89 x 89–127 x 127 mm)	4–6 1/8" (102–156 mm)	20 50
BBI-10A	35878 35879	15.43–24.14" (392–612 mm)	8 x 1/4–10 x 3/4" (203 x 6–254 x 19 mm)	5 x 5–6 x 6" (127 x 127–152 x 152 mm)	5–7 5/8" (127–194 mm)	20 50
25 kVBus Bar Size Ranges						
BBI-3A	35726 35727	3.28–3.56" (83–90 mm)	1 1/2 x 1/4–1 1/2 x 3/8" (38 x 6–38 x 10 mm)	Measure circumference	1 1/8" (29 mm)	20 50
BBI-4A	35728 35729	5.43–5.80" (138–147 mm)	2 1/2 x 3/8–2 1/2 x 5/8" (64 x 10–64 x 16 mm)	Measure circumference	1 3/4" (44 mm)	20 50
BBI-5A	35730 35731	6.67–7.18" (169–182 mm)	3 x 5/8–3 x 3/4" (76 x 16–76 x 19 mm)	Measure circumference	2 1/8–2 1/4" (54–57 mm)	20 50
BBI-6A	35732 35733	7.57–8.43" (192–214 mm)	3 1/2 x 1/2–4 x 1/4" (89 x 13–102 x 6 mm)	Measure circumference	2 1/2–2 5/8" (64–67 mm)	20 50
BBI-7A	35734 35735	8.28–10.44" (210–265 mm)	4 x 1/4–5 x 3/8" (102 x 6–127 x 10 mm)	2 1/2 x 2 1/2" (64 x 64 mm)	2 3/4–3 1/4" (70–83 mm)	20 50
BBI-8A	35736 35737	10.29–12.88" (261–327 mm)	5 x 1/4–6 x 3/4" (127 x 6–152 x 19 mm)	3 x 3" (76 x 76 mm)	3 3/8–4" (86–102 mm)	20 50
BBI-9A	35876 35877	12.29–15.31" (312–389 mm)	6 x 1/4–7 x 3/4" (152 x 6–178 x 19 mm)	3 1/2 x 3 1/2–4 x 4" (89 x 89–102 x 102 mm)	4–4 7/8" (102–124 mm)	20 50
BBI-10A	35878 35879	15.43–19.79" (392–503 mm)	8 x 1/4–9 x 3/4" (203 x 6–229 x 19 mm)	5 x 5" (127 x 127 mm)	5–6 1/4" (127–158 mm)	20 50
35 kVBus Bar Size Ranges						
BBI-7A	35734 35735	8.28–8.86" (210–225 mm)	4 x 1/4–4 x 3/4" (102 x 6–102 x 19 mm)	Measure circumference	2 3/4" (70 mm)	20 50
BBI-8A	35736 35737	10.29–10.94" (261–278 mm)	5 x 1/4–5 x 3/4" (127 x 6–127 x 19 mm)	Measure circumference	3 3/8" (86 mm)	20 50
BBI-9A	35876 35877	12.29–13.00" (312–330 mm)	6 x 1/4–6 x 3/4" (152 x 6–152 x 19 mm)	Measure circumference	4–4 1/8" (102–105 mm)	20 50
BBI-10A	35878 35879	15.43–16.86" (392–428 mm)	8 x 1/4–8 x 3/4" (203 x 6–203 x 19 mm)	Measure circumference	5–5 1/4" (127–133 mm)	20 50

Note: Rectangular and square bar sizes are based on bars having radiused edges and corners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[BBI-10A-20'](#) [BBI-7A-20'](#) [BBI-5A-50'](#) [BBI-3A-50'](#) [BBI-7A-50'](#) [BBI-3A-20'](#) [BBI-8A-50'](#) [BBI-5A-20'](#) [BBI-10A-50'](#) [BBI-8A-20'](#) [BBI-9A-50'](#) [BBI-6A-20'](#) [BBI-9A-20'](#) [BBI-4A-50'](#) [BBI-6A-50'](#)