



Spring-clamp connection, snap-in 50V, 3A

Female connector

Spring-clamp connection

Snap-in, spring-loaded





Application	Coding	Color	Part no.	Part no.
			Spring-clamp connection with strain relief Cable solid/fine-stranded 0.25 – 0.75 mm ² for cable Ø ¹⁾ 5.5 – 6.5 mm fully assembled with strain relief and locking device Cable strip length 21 mm Insul. strip length 9 mm	Snap-in, spring-loaded Cable solid/fine-stranded 0.25 – 0.75 mm ² assembled with with locking device Knock-out dimensions ²⁾ snaps into position Coding for dimming Code 2 Insul. strip length 9 mm
KNX bus 2 pole		1+ / 2- Code 1	black/green	93.421.0553.1
Dimming 2 pole		1+ / 2- Code 2	black/pastel blue	93.421.4553.1
			BST14i2 F B1 Z R1	BST14i2 F B1 R

Male connector

Spring-clamp connection

Snap-in, spring-loaded



Application	Coding	Color	Part no.	Part no.
			Spring-clamp connection with strain relief Cable solid/fine-stranded 0.25 – 0.75 mm ² for cable Ø ¹⁾ 5.5 – 6.5 mm fully assembled with strain relief and locking device Cable strip length 21 mm Insul. strip length 9 mm	Snap-in, spring-loaded Cable solid/fine-stranded 0.25 – 0.75 mm ² assembled with with locking device Knock-out dimensions ²⁾ snaps into position Coding for dimming Code 2 Insul. strip length 9 mm
KNX bus 2 pole		2- / 1+ Code 1	black/green	93.422.0553.1
Dimming 2 pole		2- / 1+ Code 2	black/pastel blue	93.422.4553.1
			BST14i2 F S1 Z R1	BST14i2 F S1 R

¹⁾ Other cables and cable cross-sections available on request
²⁾ Panel material, deburring and coating thickness may influence the knock-out dimensions.
Detailed installation instructions are available on request.