


PRODUCT NO.
SEE SHT. 2



NOTES

1. HOUSING MATERIAL: PLAIN VALOX FLAME RETARDENT, PER UL 94-VE-0 OR EQUIVALENT. COLOR WHITE
2. .100/2.54 MAX. APPLIES TO HOUSING BODY. .105/2.67 MAX. APPLIES TO BODY AND LID, AFTER LID IS CLOSED PER TMS-258-88
3. ADD 'LF' SUFFIX AT THE END OF PART NUMBERS FOR LEAD FREE OPTION.
4. IF "LF" THE P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
5. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.
6. PRODUCT SPECIFICATION: BUS-12-023.

mat'l. code		surface ISO 1302	tolerance ISO 406 ISO 1101	projection ISO 1101	product family JUMPER	
l	tr	ec	n	dr	date	
F	M06-0187	MHT	5/15/06		tolerances unless otherwise specified	
G	M07-0112	MHT	2/14/07	angles	linear	INCH/MM
H	M09-0065	MHT	4/13/09	0'±2'	linear	scale 10:1
J	BLX-N-011712	J.Z	2012-05-04	dr	J.W. BAIR	2/3/89
				enr	M.HAHN	2/3/89
				chr		
				appd	M.HAHN	2/3/89
sheet	revision	J	J			
index	sheet	1	2			

title		product family
MINI JUMP CONNECTOR ASS'Y 200 cc		JUMPER
dwg no	sheet of 2	size
65771		A3
type Product Customer Drawing		

1

2 3

4

5

6

PRODUCT NO. NOTE 3	TERMINAL		TERMINAL SPRING	
	BODY MATERIAL	CONTACT PLATING	MATERIAL	PLATING
65771-001	.010/.025 THK. 1/4 HD. BRASS ALLOY UNS C26000	1.02μ/40μ" AU OR GXT OVER 1.27μ/50μ" NICKEL	.122/.0048 THK BE-CU ALLOY	GOLD FLASH
65771-002		TIN LEAD	UNS C17200 HEAT TREATED	TIN PLATED
65771-003				
65771-004	.010/.025 THK. 1/4 HD CU-NI ALLOY UNS C72500	.03/.001 MIN THK. GOLD DOT	.122/.0048 THK BE-CU ALLOY UNS C17200 HEAT TREATED	GOLD FLASH
65771-005	.25/.010 BRASS	.76μ/30μ" AU OR GXT		GOLD FLASH

OBSOLETE

LEAD FREE OPTION

PRODUCT NO.	TERMINAL		TERMINAL SPRING	
	BODY MATERIAL	CONTACT PLATING	MATERIAL	PLATING
65771-001LF	.010/.025 THK. 1/4 HD. BRASS ALLOY UNS C26000	1.02μ/40μ" AU OR GXT OVER 1.27μ/50μ" NICKEL	.122/.0048 THK BE-CU ALLOY	GOLD FLASH
65771-002LF		TIN	UNS C17200 HEAT TREATED	TIN PLATED
65771-004LF	.010/.025 THK. 1/4 HD CU-NI ALLOY UNS C72500	.03/.001 MIN THK. GOLD DOT	.122/.0048 THK BE-CU ALLOY UNS C17200 HEAT TREATED	GOLD FLASH
65771-005LF	.25/.010 BRASS	.76μ/30μ" AU OR GXT		GOLD FLASH

mat'l. code		surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family JUMPER	
ltr ecn nchr date		tolerances unless otherwise specified		INCH/MM	title	
J		angles	linear		MINI JUMP	
		0°±2'		scale 10:1	CONNECTOR ASS'Y 200 cc	
		dr	J.W. BAIR	2/3/89	dwg no	shee 2 of 2 size
		engr	M.HAHN	2/3/89	65771	A3
		chr			type Product Customer Drawing	
		appd	M.HAHN	2/3/89		
sheet index	revision sheet					

