

Search within category

GO

BUY NOW

DESIGN / INSTALL



VB0D2B4CM48M1

The 32A, 230V single-phase vertical power strip in black has 48 IEC C-13 receptacles. It features four 16A single-pole magnetic breaker on-off switches with integral switch guard and dual 10' (3m) power cords with an IEC 60309 - 2P+ E pin in-sleeve connector. It complies with IEC 60950-1, EN 55022, and EN 55024 and is CE Marked. It measures 66.3H x 3.4W x 2.0D (1683mm x 89mm x 51mm). It is sold individually.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
CE Compliant	Yes			
Rack PDU Type	Basic Rack PDU			
Monitoring	NA			
Remote Outlet Switching	No			
Mount Orientation	Vertical			
Current Rating (Amps)	32A			
Input Voltage	230V - Single Phase			
Plug Type	(2) IEC 60309 - 6H 2P+E Blue Splashproof			
Output Voltage	230V			
Receptacle Type	IEC C-13			
Total Number of Outlets	48			
Depth (In.)	2.00			
Depth (mm)	50.8			
Height (In.)	66.25			
Height (mm)	1682.8			
Width (In.)	3.50			
Width (mm)	88.9			
Tool-Less Button Spacing (In.)	64.75			
Tool-Less Button Spacing (mm)	1644.7			
No. of Rack Spaces	0			
Surge Suppression	No			
Amps	32A			
Cable Length	3			
Length (In.)	71.50			
UL Recognized	No			
Voltage	230V			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			