



| REV. | DATE     | DESCRIPTION           |
|------|----------|-----------------------|
| A    | 03/18/05 | UPDATE DRAWING FORMAT |



NOTES: FINISH {PLATING THICKNESS IN MICRO-INCHES}

1. NICKEL PL. 100 MIN. OVER COPPER PL. 50 MIN.  
OVER COPPER PL. 50 MIN.
2. GOLD PL. 30 MIN. OVER NICKEL PL. 50 MIN.
3. TEFLON MIL-P-19468.

|             |             |              |         |          |                                                                                                                                        |     |                      |  |                   |  |                          |  |                                                                                  |  |  |          |  |                        |  |  |  |  |
|-------------|-------------|--------------|---------|----------|----------------------------------------------------------------------------------------------------------------------------------------|-----|----------------------|--|-------------------|--|--------------------------|--|----------------------------------------------------------------------------------|--|--|----------|--|------------------------|--|--|--|--|
|             |             |              |         |          | UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR DIMENSION REFERENCE ONLY.            |     | APPROVALS            |  | DATE              |  | <h1>Amphenol Connex</h1> |  |                                                                                  |  |  |          |  |                        |  |  |  |  |
| 8           |             |              |         |          | UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:<br>0.5 - 8mm ± 0.20mm<br>8 - 30mm ± 0.40mm<br>30 - 120mm ± 0.50mm           |     | DRAWN                |  | C.R.S.            |  |                          |  |                                                                                  |  |  | 03/18/05 |  |                        |  |  |  |  |
| 7           | FERRULE     | COPPER       | NICKEL  | 1        |                                                                                                                                        |     | CHECKED              |  |                   |  |                          |  |                                                                                  |  |  |          |  |                        |  |  |  |  |
| 6           | HEX NUT     | BRASS        | NICKEL  | 1        |                                                                                                                                        |     | ISSUED               |  |                   |  |                          |  | PART DESCRIPTION<br><br>BNC BULKHEAD CRIMP JACK<br>(FOR AT&T 735A CABLE - 75ohm) |  |  |          |  |                        |  |  |  |  |
| 5           | LOCK WASHER | BRASS        | NICKEL  | 1        |                                                                                                                                        |     | SHEET                |  | 1 OF 1            |  |                          |  |                                                                                  |  |  |          |  | PART NO.<br><br>112969 |  |  |  |  |
| 4           | GASKET      | SILICONE     | RED     | 1        |                                                                                                                                        |     |                      |  |                   |  |                          |  |                                                                                  |  |  |          |  |                        |  |  |  |  |
| 3           | CONTACT PIN | PHOS. BRONZE | GOLD    | 1        |                                                                                                                                        |     |                      |  |                   |  |                          |  |                                                                                  |  |  |          |  |                        |  |  |  |  |
| 2           | INSULATOR   | TEFLON       | NATURAL | 1        | UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:<br>.020 - .315 = ± 0.007"<br>.315 - 1.180 = ± 0.015"<br>1.180 - 4.724 = ± 0.020" |     | CAD FILE             |  | C:/112/112969.DWG |  |                          |  | DWG. NO. 112969.DWG<br>REV. A<br>SIZE A<br>SCALE NA                              |  |  |          |  |                        |  |  |  |  |
| 1           | BODY        | BRASS        | NICKEL  | 1        |                                                                                                                                        |     |                      |  |                   |  |                          |  |                                                                                  |  |  |          |  |                        |  |  |  |  |
| DESCRIPTION |             |              |         | MATERIAL | FINISH                                                                                                                                 | QTY | DO NOT SCALE DRAWING |  |                   |  |                          |  |                                                                                  |  |  |          |  |                        |  |  |  |  |