

B-424 Paper Material

Color: White Finish: Matte

White paper material with matte finish and smooth top coat finish for thermal transfer printing. Good contrast and smear resistance for thermal barcode printing. Used for general purpose labeling applications.

Performance Attributes:




Figure 2




Figure 3



Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 2	THT-17-424-3	Paper	White	2.000 (50.8)	1.000 (25.4)	1.125 (28.6)	2.200 (55.9)	1	3,000	R4302
Fig. 2	THT-53-424-3	Paper	White	2.000 (50.8)	0.500 (12.7)	0.600 (15.2)	2.200 (55.9)	1	3,000	R4302
Fig. 2	THT-166-424-2	Paper	White	2.500 (63.5)	1.250 (31.8)	1.375 (34.9)	2.700 (68.6)	1	2,000	R4300
Fig. 2	THT-7-424-3	Paper	White	2.750 (69.9)	1.250 (31.8)	1.375 (34.9)	2.950 (74.9)	1	3,000	R4300
Fig. 2	THT-18-424-3	Paper	White	3.000 (76.2)	1.000 (25.4)	1.125 (28.6)	3.200 (81.3)	1	3,000	R4300
Fig. 2	THT-19-424-1	Paper	White	3.000 (76.2)	2.000 (50.8)	2.125 (54.0)	3.200 (81.3)	1	1,000	R4300
Fig. 2	THT-20-424-1	Paper	White	3.000 (76.2)	5.000 (127.0)	5.125 (130.2)	3.200 (81.3)	1	1,000	R4300
Fig. 3	THT-21-424	Paper	White	3.000 (76.2)	300 ft. (91.4 m)	300 ft. (91.4 m)	3.200 (81.3)	1	1 Roll Cont.	R4300
Fig. 2	THT-25-424-1	Paper	White	4.000 (101.6)	6.000 (152.4)	6.125 (155.6)	4.200 (106.7)	1	1,000	R4307
Fig. 2	THT-55-424-1	Paper	White	4.000 (101.6)	2.000 (50.8)	2.125 (54.0)	4.200 (106.7)	1	1,000	R4307
NOTICE BBP®12 PRINTER ONLY: The following part numbers ending with "-SC" are 1" Small Core Rolls for use in the BBP12 Printer only.										
Fig. 2	THT-17-424-1.5-SC	Paper	White	2.000 (50.8)	1.000 (25.4)	1.125 (28.6)	2.200 (55.9)	1	1,500	R4313
Fig. 2	THT-18-424-1.5-SC	Paper	White	3.000 (76.2)	1.000 (25.4)	1.125 (28.6)	3.200 (81.3)	1	1,500	R4313



B-425 Polypropylene Material

Color: White Finish: Matte

White polypropylene material stock with matte/opaque finish for thermal transfer printing or write-on applications. Excellent solvent resistance and print performance; not recommended for long-term outdoor use.

Performance Attributes:




Figure 1




Figure 2



Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horiz. Repeat C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 1	THT-5-425-10	Polypropylene	White	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	10,000	R4307
Fig. 2	THT-17-425-3	Polypropylene	White	2.000 (50.8)	1.000 (25.4)	-	1.125 (28.6)	2.200 (55.9)	1	3,000	R4302
Fig. 2	THT-7-425-3	Polypropylene	White	2.750 (69.9)	1.250 (31.8)	-	1.375 (34.9)	2.950 (74.9)	1	3,000	R4300
Fig. 2	THT-18-425-3	Polypropylene	White	3.000 (76.2)	1.000 (25.4)	-	1.125 (28.6)	3.200 (81.3)	1	3,000	R4300
Fig. 2	THT-20-425-1	Polypropylene	White	3.000 (76.2)	5.000 (127.0)	-	5.125 (130.2)	3.200 (81.3)	1	1,000	R4300
Fig. 2	THT-55-425-1	Polypropylene	White	4.000 (101.6)	2.000 (50.8)	-	2.125 (54.0)	4.200 (106.7)	1	1,000	R4307
Fig. 2	THT-76-425-1	Polypropylene	White	4.000 (101.6)	3.000 (76.2)	-	3.125 (79.4)	4.200 (106.7)	1	1,000	R4307
NOTICE BBP®12 PRINTER ONLY: The following part numbers ending with “-SC” are 1” Small Core Rolls for use in the BBP12 Printer only.											
Fig. 2	THT-17-425-1.5-SC	Polypropylene	White	2.000 (50.8)	1.000 (25.4)	-	1.125 (28.6)	2.200 (55.9)	1	1,500	R4313
Fig. 2	THT-18-425-1.5-SC	Polypropylene	White	3.000 (76.2)	1.000 (25.4)	-	1.125 (28.6)	3.200 (81.3)	1	1,500	R6213



B-430 Polyester Material

Color: Clear Finish: Gloss

Translucent, high performance polyester material with a glossy finish. Non-colored material with permanent adhesive. Good for general purpose thermal transfer printing.

Performance Attributes:




Figure 3




Figure 6




Figure 9



Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horiz. Repeat C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 6	THT-149-430-10	Polyester	Clear	0.500 (12.7)	0.500 (12.7)	0.600 (15.2)	0.625 (15.9)	2.500 (63.5)	4	10,000	R6002
Fig. 6	THT-39-430-10	Polyester	Clear	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.625 (15.9)	3.350 (85.1)	3	10,000	R6007
Fig. 9	THT-17-430-3	Polyester	Clear	2.000 (50.8)	1.000 (25.4)	-	1.125 (28.6)	2.200 (55.9)	1	3,000	R6000
Fig. 9	THT-18-430-3	Polyester	Clear	3.000 (76.2)	1.000 (25.4)	-	1.125 (28.6)	3.200 (81.3)	1	3,000	R6002
Fig. 9	THT-19-430-1	Polyester	Clear	3.000 (76.2)	2.000 (50.8)	-	2.125 (54.0)	3.200 (81.3)	1	1,000	R6002
Fig. 3	THT-21-430	Polyester	Clear	3.000 (76.2)	300 ft. (91.4 m)	-	300 ft (91.4 m)	3.200 (81.3)	1	1 Roll Cont.	R6002
NOTICE BBP®12 PRINTER ONLY: The following part numbers ending with “-SC” are 1” Small Core Rolls for use in the BBP12 Printer only.											
Fig. 9	THT-17-430-1.5-SC	Polyester	Clear	2.000 (50.8)	1.000 (25.4)	-	1.125 (28.6)	2.200 (55.9)	1	1,500	R6013
Fig. 9	THT-18-430-1.5-SC	Polyester	Clear	3.000 (76.2)	1.000 (25.4)	-	1.125 (28.6)	3.200 (81.3)	1	1,500	R6013