




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CMR19X84NU	28.00 LB/EACH (12.70 KG/EACH)

- NOTES:
- CAN BE USED WITH ANY INDUSTRY STANDARD 19" COMPONENTS IN ADDITION TO ALL PANDUIT CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
 - WILL HOLD UP TO 45 SINGLE RACK SPACINGS.
 - EIA SPACING ON RACK: I.E., REF.
HOLE SPACING ON UPRIGHT CHANNELS:
.625, .625, .500, .625, .625, .500, ETC.
 - ASSEMBLY IS REQUIRED.
 - RACK PART THICKNESSES:
 - UPRIGHT CHANNELS: WEB; .14 ±.03
FLANGE; .19 ±.03
 - TOP BRACKET: .25 ±.03
 - BASE BRACKET: .25 ±.03
 - DIMENSIONS IN PARENTHESIS ARE IN METRIC.
 - ALL ASSEMBLY HARDWARE INCLUDED:
 - (12) 3/8-16 X 1" BLACK HEX HEAD CAP SCREW
 - (12) 3/8" PAINT PIERCING GROUNDING WASHER
 - (1) TUBE OF ANTI-OXIDIZING PASTE
 - (24) 12-24 X .5" SLOTTED PAN HEAD STEEL SCREWS
 - (12) 3/8-16 BLACK HEX NUTS
 - TESTED AND APPROVED 1000 LBS LOAD RATING BY UNDERWRITERS LABORATORIES.
 - RU SPACING NUMBERS ARE CLEARLY PRINTED ON MOUNTING RAILS. RU NUMBERING IS BOTTOM-UP, WITH RU #1 AT BOTTOM AND RU #45 AT TOP.

MODEL FILENAME		V10073AC/02	
CAD FILENAME/LAYERS		V10073AC_DC/02A	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
CABLE MANAGEMENT RACK (CMR19X84NU) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY TKW	MAT'L: ALUMINUM		SCALE NONE
DATE 09-30-04			DRAWING NO. 10073-21
CHK'D KRKE			DWG A SIZE

O2A	11-11-08	BAME	DPM	CHANGED NUMBERING ORIENTATION UPDATED HARDWARE NOTE LOAD RATING WAS 800 LBS. ADDED NOTE 9	10073-21				
R	9-30-04	TKW	KRKE	RELEASED TO PRODUCTION	10073-21		RTSU	RTSU	
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	