



1830

L4™

The L4™ is a handy, unbelievably bright LED flashlight that's powered by 3 AAAA alkaline cells (included). The light weight, slim profile design fits neatly in your pocket and comfortably in your hand. A tail button switch provides quick on/off or momentary activation. The clip is virtually unbreakable because it is molded to the Xenoy body as one unit. And because it is molded out of polycarbonate resin, it won't cause sparks and is safe to use in electrical environments.

- 50+ hours of battery life
- Built Pelican tough
- Light weight, comfortable and well-balanced
- Unconditional Lifetime Guarantee of Excellence



DIMENSIONS

Length	6.20" (15.7 cm)
---------------	-----------------

MATERIALS

Body	Xenoy
O-Ring	Polymer
Shroud	Xenoy
Contact Spring Retainer	Aluminum

COLOURS

High Visibility Yellow

LIGHT SPECS

Lamp Type	LED
------------------	-----

POWER

Battery Size	AAAA
Battery Type	Alkaline
Battery Quantity	3
Batteries Included	yes
Volts	4.5v

WEIGHT

Weight With Batteries	1.2 oz (34 gr)
Weight Without Batteries	0.6 oz (17 gr)
Packaged Weight	1.2 oz (34 gr)

SWITCH

Switch Type	Push Button
--------------------	-------------

Light Modes

On / Off

Pelican


23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311

CERTIFICATIONSsales@pelican.com • www.pelican.com**Class I, Division 1***Document created on 08-22-20***Class I, Division 2****OTHER****Minimum Pack**

6

Package Code

C

FL1 STANDARD	HIGH
	5 LUMENS
	32h 0mins
	13m
	44cd
	IPX4

ACCESSORIES