


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.*	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS- SECTION	WEIGHT lbs./100pcs. (g)	RECOMMENDED HOLE SIZE FOR THROUGH PANEL MOUNTING
	MIN. in (mm)	MAX. in (mm)										
SST2HH	.06 (1.5)	2.00 (50)	.062 (1.6)	.300 (7.6)	.472 (11.9)	.250 (6.4)	.590 (14.9)	8.5 (216)	120 (534)	HEAVY	.802 (364)	.316/.520 (8.0/13.2)
SST4HH	.06 (1.5)	4.00 (102)	.062 (1.6)	.300 (7.6)	.472 (11.9)	.250 (6.4)	.590 (14.9)	14.8 (376)	120 (534)	HEAVY	1.3 (538)	.316/.520 (8.0/13.2)

NOTES:

*1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

W10001EA/09-SS-17819

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										STA-STRAP CABLE TIES (HEAVY HEAD)	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .0005 (.XXX) ± .0015 (.XX) ± .02(.5) ANGLES ± .0005	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY L.VALDES	MAT'L: NYLON 6.6
9	11/29/10	JABO	TGS	CHANGED NOTE 1, AND CORRECTED SST2HH LENGTH FROM 8.0 TO 8.5		SS-17819	9	TGS		DATE 11/10/82	DRAWING NO. SS-17819
REV	DATE	BY	CHK	DESCRIPTION		ECN	-	R	CUST	SUP	CHK'D HVP
										DWG A SIZE	